

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1200880116](#)  
**Status:** **Active**  
**Overview:** [Brad Nano-Change \(M8\) Products](#)  
**Description:** Nano-Change (M8) Single-Ended Cordset, 4 Poles, Female (Straight) with Snap Coupling to Pigtail, 24 AWG, PUR Cable, 4 Poles, 2.0m (6.56') Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR6837  
 UL E152210

**General**

Product Family Industrial Cordsets  
 Series [120088](#)  
 Connector End A Nano-Change (M8)  
 Connector End B Pigtail  
 IP Rating IP67  
 Material - Contact Copper Alloy  
 Overview [Brad Nano-Change \(M8\) Products](#)  
 Product Name Nano-Change (M8)  
 Protocol N/A  
 Region America  
 Type Single Ended  
 UPC 78678805018

**Physical**

Cable Diameter 4.32mm (.170")  
 Cable Length 2.0m (6.56')  
 Color - Cable Jacket Yellow  
 Coupling Style Snap  
 Gender Female-Pigtail  
 Keyway None  
 LED Indicator No  
 Material - Cable Jacket PUR  
 Material - Connector Body TPE  
 Material - Coupling Nut N/A  
 Material - Plating Mating Gold  
 Orientation Straight to Pigtail  
 Poles 4  
 Temperature Range - Operating -25° to +80°C  
 Wire Size AWG 24  
 Wire/Cable Type E152210

**Electrical**

Current - Maximum per Contact 3.0A  
 Voltage - Maximum 60V AC / 75V DC

**Material Info**

Engineering Number 504000B09M020

**Reference - Drawing Numbers**

Sales Drawing SD-120088-028-001

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

**China RoHS**

**Search Parts in this Series**

[120088 Series](#)

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1200880116](#)