

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1210360832](#)  
**Status:** **Active**  
**Overview:** mPm DIN Valve Connectors  
**Description:** Micro-Change (M12) to Brad mPm DIN Form C - 8mm Cordset, C4 Circuit, Yellow LED, 5 Poles, Male (90°), Black PUR Cable, 0.60m (1.97') Length, 24V

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Industrial Cordsets
Series	<a href="#">121036</a>
Connector End A	Brad mPm DIN C - 8mm
Connector End B	Micro-Change (M12)
IP Rating	IP65
Material - Contact	Copper Alloy
Overview	<a href="#">mPm DIN Valve Connectors</a>
Product Name	Micro-Change (M12), mPm
Protocol	N/A
Region	America, Europe
Type	Double Ended
UPC	887191228204

**Physical**

Cable Diameter	5.72mm (.225")
Cable Length	0.60m (1.97')
Color - Cable Jacket	Black
Coupling Style	Threaded
Gender	Male-Male
Keyway	Single
LED Indicator	Yellow
Material - Cable Jacket	PUR
Material - Connector Body	Polypropylene
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	52.895/g
Orientation	90° to Straight
Poles	5
Temperature Range - Operating	-25° to +75°C
Wire Size AWG	20
Wire/Cable Type	PUR

**Electrical**


Current - Maximum per Contact	1.5A
Voltage - Maximum	24V

**Material Info**

Engineering Number	H850B2P12M006
--------------------	---------------

**Reference - Drawing Numbers**

Sales Drawing	SD-121036-004-001
---------------	-------------------



*Series image - Reference only*

**EU ELV**

**Not Compliant**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Contained Per - D(2020)9139-DC (19 Jan 2021)

Lead

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Compliant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[121036 Series](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1210360832](#)