

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1552200239](#)
Status: **Active**
Overview: Flamar Standard and Custom Cables for Industrial Automation
Description: Flamar Control Cable, WSOR Jacket, Unshielded, 5 Circuits, 1.50mm² with Green-Yellow Ground / 16 AWG with Green-Yellow Ground, 8.60mm (.339") Diameter, 500.0m (1640.42') Length, Gray

Documents:

[Product Specification 1552200001-P1E \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Brochure \(PDF\)](#)

Agency Certification

UL E172949

General

Product Family Cable
Series [155220](#)
Crimp Quality Equipment Yes
Geographic Area Global
Overview [Flamar Standard and Custom Cables for Industrial Automation](#)
Product Name Flamar, Signal and Control
UPC 889056461436

Physical

Bending Radius - Minimum > 7.5xOD
Cable Length 500.0m
Circuits (Loaded) 5
Color - Cable Jacket Gray
Insulation TPE
Material - Outer Jacket WSOR
Net Weight 0.121/kg
Outer Jacket Diameter 8.60mm
Packaging Type Reel
Temperature Range - Operating -25° to +80°C
Wire Size AWG 16
Wire Size mm² 1.50
Wire/Cable Type UL AWM 21215 / CSA

Electrical


Current - Maximum per Contact Contact Molex
Voltage - Maximum 600V

Material Info

Engineering Number 1X500M

Reference - Drawing Numbers

Product Specification 1552200001-P1E



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[155220 Series](#)

Use With

DIN Valve Connectors [121201](#) , [121202](#)
, [121207](#) , [121208](#) , [121205](#) , [121211](#)

Micro-Change (M12) [120071](#)
Ultra-
Lock (M12) [120085](#)
GWconnect Heavy
Duty Connectors [93601](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[155220-0239](#)