

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1552210013](#)
Status: **Active**
Overview: Flamar Standard and Custom Cables for Industrial Automation
Description: Flamar Sensor Cable, WSOR Jacket, Braided Shielding Overall, 4 Circuits, 0.34mm² / 22 AWG, 5.70mm (.224") Diameter, 300.0m (984.25') Length, Black

Documents:

[Product Specification 1552200001-P1E \(PDF\)](#)
[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E172949

General

Product Family Cable
 Series [155221](#)
 Comments 3 reels of 100.0m each
 Crimp Quality Equipment Yes
 Geographic Area Global
 Overview [Flamar Standard and Custom Cables for Industrial Automation](#)
 Product Name Flamar, Signal and Control
 UPC 889056463850

Physical

Bending Radius - Minimum > 7.5xOD
 Cable Length 300.0m
 Circuits (Loaded) 4
 Color - Cable Jacket Black
 Insulation TPE
 Material - Outer Jacket WSOR
 Net Weight 0.047/kg
 Outer Jacket Diameter 5.70mm
 Packaging Type Reel
 Temperature Range - Operating -25° to +80°C
 Wire Size AWG 22
 Wire Size mm² 0.34
 Wire/Cable Type UL AWM 21215 / CSA

Electrical

Current - Maximum per Contact Contact Molex
 Voltage - Maximum 600V

Material Info

Engineering Number BS1-4-3X100M

Reference - Drawing Numbers

Product Specification 1552200001-P1E



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series

[155221](#) Series

Use With

Nano-Change (M8) [120091](#) , Micro-Change (M12) [120071](#) , Ultra-Lock (M12) [120085](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[155221-0013](#)