

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1511181666](#)

**Status:** **Active**

**Overview:**

**Description:** 2.00mm Pitch, Milli-Grid PCB Header, Dual Row, Vertical, Surface Mount, 0.38µm Gold (Au) Plating, with Peg, with Pick and Place Cap, 16 Circuits, Glow-Wire Capable, Tube

**Agency Certification**

|     |         |
|-----|---------|
| CSA | LR19980 |
| UL  | E29179  |

**General**

|                |                                       |
|----------------|---------------------------------------|
| Product Family | PCB Headers                           |
| Series         | 151118                                |
| Application    | Board-to-Board, Signal, Wire-to-Board |
| Overview       | milligrd                              |
| Product Name   | Milli-Grid                            |
| UPC            | 889056798075                          |

**Physical**

|                                |                        |
|--------------------------------|------------------------|
| Breakaway                      | No                     |
| Circuits (Loaded)              | 16                     |
| Circuits (maximum)             | 16                     |
| Color - Resin                  | Black                  |
| First Mate / Last Break        | No                     |
| Flammability                   | 94V-0                  |
| Glow-Wire Capable              | Yes                    |
| Guide to Mating Part           | No                     |
| Keying to Mating Part          | None                   |
| Lock to Mating Part            | Yes                    |
| Material - Metal               | Copper Alloy           |
| Material - Plating Mating      | Gold                   |
| Material - Plating Termination | Tin                    |
| Material - Resin               | Liquid Crystal Polymer |
| Net Weight                     | 0.738/g                |
| Number of Rows                 | 2                      |
| Orientation                    | Vertical               |
| PCB Locator                    | No                     |
| PCB Retention                  | Yes                    |
| Packaging Type                 | Tube                   |
| Pitch - Mating Interface       | 2.00mm                 |
| Pitch - Termination Interface  | 2.00mm                 |
| Plating min - Mating           | 0.380µm                |
| Plating min - Termination      | 2.000µm                |
| Polarized to Mating Part       | Yes                    |
| Polarized to PCB               | No                     |
| Robotic Placement              | Pick and Place Cap     |
| Shrouded                       | Yes                    |
| Stackable                      | No                     |
| Surface Mount Compatible (SMC) | Yes                    |
| Temperature Range - Operating  | -55° to +105°C         |
| Termination Interface: Style   | Surface Mount          |

**Electrical**

|                               |         |
|-------------------------------|---------|
| Current - Maximum per Contact | 2.0A    |
| Voltage - Maximum             | 125V AC |

**Solder Process Data**

|  |     |
|--|-----|
| Duration at Max. Process Temperature (seconds) | 010 |
|--|-----|

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[151118](#) Series

**Mates With**

Milli-Grid Receptacle Housing [151192](#) ,  
[51110](#) <br> Milli-Grid PCB Receptacles  
[78787](#) , [78788](#) , [79107](#) , [79109](#)

Lead-freeProcess Capability  
Max. Cycles at Max. Process Temperature  
Process Temperature max. C

REFLOW  
001  
260

**Material Info**

**Reference - Drawing Numbers**

Application Specification 503940001-AS-000, 503940002-AS-000  
Packaging Specification PK-151118-0001-001, PK-151118-3000-001  
Product Specification PS-151117-0001-001  
Sales Drawing SD-151118-0001-001

This document was generated on 09/02/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[151118-1666](#)