

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1552109021](#)
Status: **Active**
Overview: Flamar Standard and Custom Cables for Industrial Automation
Description: Flamar Distribution Box Cable, PVC Jacket, Unshielded, 19 Circuits, 3x(0.75mm²) with Green-Yellow Ground + 16x(0.34mm²) / 3x(19 AWG) with Green-Yellow Ground + 16x(22 AWG), 10.20mm (.402") Diameter, 1000.0m (3280.83') Length, Black

Documents:

[Product Specification 1552109001-P1E \(PDF\)](#)
[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E172949

General

Product Family Cable
 Series [155210](#)
 Crimp Quality Equipment Yes
 Geographic Area Global
 Overview [Flamar Standard and Custom Cables for Industrial Automation](#)
 Product Name Flamar, Signal and Control
 UPC 889056455633

Physical

Bending Radius - Minimum > 15xOD
 Cable Length 1000.0m
 Circuits (Loaded) 19 (3+16)
 Color - Cable Jacket Black
 Insulation TPE
 Material - Outer Jacket PVC
 Net Weight 0.150/kg
 Outer Jacket Diameter 10.20mm
 Packaging Type Wooden Drum
 Temperature Range - Operating +5° to +80°C
 Wire Size AWG 19, 22
 Wire Size mm² 0.34, 0.75
 Wire/Cable Type UL AWM 2464 / CSA

Electrical

Current - Maximum per Contact Contact Molex
 Voltage - Maximum 300V

Material Info

Engineering Number 1X1000M

Reference - Drawing Numbers

Product Specification 1552109001-P1E



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 D(2020)9139-DC (19
 Jan 2021)

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[155210 Series](#)

Use With

Brad M23 [120230](#) , [120233](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[155210-9021](#)