

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1552110003](#)
Status: **Active**
Overview: Flamar Standard and Custom Cables for Industrial Automation
Description: Flamar Sensor Cable, PVC Jacket, Braided Shielding Overall, 3 Circuits, 0.34mm² / 22 AWG, 5.40mm (.213") Diameter, 1500.0m (4921.26') Length, Black

Documents:

[Product Specification 1552100001-P1E \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Brochure \(PDF\)](#)

Agency Certification

UL E172949

General

Product Family Cable
Series [155211](#)
Crimp Quality Equipment Yes
Geographic Area Global
Overview [Flamar Standard and Custom Cables for Industrial Automation](#)
Product Name Flamar, Signal and Control
UPC 889056455695

Physical

Bending Radius - Minimum > 15xOD
Cable Length 1500.0m
Circuits (Loaded) 3
Color - Cable Jacket Black
Insulation TPE
Material - Outer Jacket PVC
Net Weight 0.042/kg
Outer Jacket Diameter 5.40mm
Packaging Type Reel
Temperature Range - Operating +5° to +80°C
Wire Size AWG 22
Wire Size mm² 0.34
Wire/Cable Type UL AWM 2464 / CSA

Electrical

Current - Maximum per Contact Contact Molex
Voltage - Maximum 300V

Material Info

Engineering Number 1X1500M

Reference - Drawing Numbers

Product Specification 1552100001-P1E



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[155211 Series](#)

Use With

Nano-Change (M8) [120091](#) , Micro-Change (M12) [120071](#) , Ultra-Lock (M12) [120085](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[155211-0003](#)