

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1552110006](#)
Status: **Active**
Overview: Flamar Standard and Custom Cables for Industrial Automation
Description: Flamar Sensor Cable, PVC Jacket, Braided Shielding Overall, 3 Circuits, 0.34mm² / 22 AWG, 5.40mm (.213") Diameter, 1500.0m (4921.26') Length, Gray

Documents:

[Product Specification 1552100001-P1E \(PDF\)](#)
[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E172949

General

Product Family Cable
 Series [155211](#)
 Crimp Quality Equipment Yes
 Geographic Area Global
 Overview [Flamar Standard and Custom Cables for Industrial Automation](#)
 Product Name Flamar, Signal and Control
 UPC 889056455824

Physical

Bending Radius - Minimum > 15xOD
 Cable Length 1500.0m
 Circuits (Loaded) 3
 Color - Cable Jacket Gray
 Insulation TPE
 Material - Outer Jacket PVC
 Net Weight 0.042/kg
 Outer Jacket Diameter 5.40mm
 Packaging Type Reel
 Temperature Range - Operating +5° to +80°C
 Wire Size AWG 22
 Wire Size mm² 0.34
 Wire/Cable Type UL AWM 2464 / CSA

Electrical


Current - Maximum per Contact Contact Molex
 Voltage - Maximum 300V

Material Info

Engineering Number 1X1500M

Reference - Drawing Numbers

Product Specification 1552100001-P1E



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 D(2020)9139-DC (19
 Jan 2021)

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[155211 Series](#)

Use With

Nano-Change (M8) [120091](#) , Micro-Change (M12) [120071](#) , Ultra-Lock (M12) [120085](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[155211-0006](#)