

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1552200022](#)  
**Status:** **Active**  
**Overview:** Flamar Standard and Custom Cables for Industrial Automation  
**Description:** Flamar Sensor Cable, WSOR Jacket, Unshielded, 4 Circuits, 0.25mm<sup>2</sup> / 24 AWG, 4.80mm (.189") Diameter, 600.0m (1968.50') Length, Orange

**Documents:**

[Product Specification 1552200001-P1E \(PDF\)](#)  
[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Cable
Series	<a href="#">155220</a>
Comments	3 reels of 200.0m each
Crimp Quality Equipment	Yes
Geographic Area	Global
Overview	<u>Flamar Standard and Custom Cables for Industrial Automation</u>
Product Name	Flamar, Signal and Control
UPC	889056457064

**Physical**

Bending Radius - Minimum	> 7.5xOD
Cable Length	600.0m
Circuits (Loaded)	4
Color - Cable Jacket	Orange
Insulation	TPE
Material - Outer Jacket	WSOR
Net Weight	0.010/g
Outer Jacket Diameter	4.80mm
Packaging Type	Reel
Temperature Range - Operating	-25° to +80°C
Wire Size AWG	24
Wire Size mm <sup>2</sup>	0.25
Wire/Cable Type	UL AWM 21215 / CSA

**Electrical**


Current - Maximum per Contact	Contact Molex
Voltage - Maximum	600V

**Material Info**

Engineering Number	B49-4-3X200M
--------------------	--------------

**Reference - Drawing Numbers**

Product Specification	1552200001-P1E
-----------------------	----------------



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[155220 Series](#)

**Use With**

Nano-Change (M8) [120091](#) , Micro-Change (M12) [120071](#) , Ultra-Lock (M12) [120085](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[155220-0022](#)