

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1552200036](#)
Status: **Active**
Overview: Flamar Standard and Custom Cables for Industrial Automation
Description: Flamar Sensor Cable, WSOR Jacket, Unshielded, 8 Circuits, 0.25mm² / 24 AWG, 6.40mm (.252") Diameter, 1000.0m (3280.83') Length, Black

Documents:

[Product Specification 1552200001-P1E \(PDF\)](#)
[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E172949

General

Product Family Cable
 Series [155220](#)
 Crimp Quality Equipment Yes
 Geographic Area Global
 Overview [Flamar Standard and Custom Cables for Industrial Automation](#)
 Product Name Flamar, Signal and Control
 UPC 889056457309

Physical

Bending Radius - Minimum > 7.5xOD
 Cable Length 1000.0m
 Circuits (Loaded) 8
 Color - Cable Jacket Black
 Insulation TPE
 Material - Outer Jacket WSOR
 Net Weight 0.057/kg
 Outer Jacket Diameter 6.40mm
 Packaging Type Reel
 Temperature Range - Operating -25° to +80°C
 Wire Size AWG 24
 Wire Size mm² 0.25
 Wire/Cable Type UL AWM 21215 / CSA

Electrical


Current - Maximum per Contact Contact Molex
 Voltage - Maximum 600V

Material Info

Engineering Number B41-8-1X1000M

Reference - Drawing Numbers

Product Specification 1552200001-P1E



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 D(2020)9139-DC (19
 Jan 2021)

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[155220 Series](#)

Use With

Nano-Change (M8) [120091](#) , Micro-Change (M12) [120071](#) , Ultra-Lock (M12) [120085](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[155220-0036](#)