

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1554116004](#)

Status: **Active**

Overview: [Flamar Standard and Custom Cables for Industrial Automation](#)

Description: Flamar Ethernet 5e Network Cable, PVC Jacket, Braided Shielding Overall, 8 Circuits, 4x(2x0.14mm²) / 4x(2x26 AWG), 7.20mm (.283") Diameter, 300.0m (984.25') Length, Teal

Documents:

[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E172949

General

Product Family	Cable
Series	155411
Comments	3 reels of 100.0m each
Crimp Quality Equipment	Yes
Geographic Area	Global
Overview	Flamar Standard and Custom Cables for Industrial Automation
Product Name	Flamar, Network
Protocol	EtherNet 5e
UPC	889056463522

Physical

Bending Radius - Minimum	> 15xOD
Cable Length	300.0m
Circuits (Loaded)	8
Color - Cable Jacket	Teal
Insulation	PE
Material - Outer Jacket	PVC
Net Weight	0.062/kg
Outer Jacket Diameter	7.20mm
Packaging Type	Reel
Temperature Range - Operating	+5° to +60°C
Wire Size AWG	26
Wire Size mm ²	0.14
Wire/Cable Type	UL AWM 2464 / CSA

Electrical

Current - Maximum per Contact	Contact Molex
Voltage - Maximum	300V

Material Info

Engineering Number 3X100M



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[155411 Series](#)

Use With

Micro-Change (M12) [130047](#) , [120100](#) , [130034](#) , [120071](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[155411-6004](tel:1554116004)