

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1554212003](#)  
**Status:** **Active**  
**Overview:** Flamar Standard and Custom Cables for Industrial Automation  
**Description:** Flamar CC-Link Network Cable, WSOR Jacket, Braided Shielding Overall, 3 Circuits, 0.50mm<sup>2</sup> / 20 AWG, 7.70mm (.303") Diameter, 100.0m (328.08') Length, Red

**Documents:**

[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Cable
Series	<a href="#">155421</a>
Crimp Quality Equipment	Yes
Geographic Area	Global
Overview	<a href="#">Flamar Standard and Custom Cables for Industrial Automation</a>
Product Name	Flamar, Network
Protocol	CC-Link
UPC	889056464208

**Physical**


Bending Radius - Minimum	> 15xOD
Cable Length	1000.0m
Circuits (Loaded)	3
Color - Cable Jacket	Red
Insulation	Foam PE
Material - Outer Jacket	WSOR
Net Weight	0.010/g
Outer Jacket Diameter	7.70mm
Packaging Type	Reel
Temperature Range - Operating	-10° to +60°C
Wire Size AWG	20
Wire Size mm <sup>2</sup>	0.50
Wire/Cable Type	UL AWM 21215 / CSA

**Electrical**

Current - Maximum per Contact	Contact Molex
Voltage - Maximum	600V

**Material Info**

Engineering Number	1X1000M
--------------------	---------



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[155421](#) Series

**Use With**

Micro-Change (M12) [130047](#) , [120100](#) , [130034](#) , [120071](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[155421-2003](#)