

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1713201022](#)  
**Status:** **Active**  
**Overview:** [Impel and Impel Plus Backplane Solutions](#)  
**Description:** Impel 90 Ohm, 4 Pair Right-Angle Daughtercard, 1.90mm Pitch, Unguided, 12 Columns, 96 Circuits, Plated Through Hole Dimension 0.36mm

**Documents:**

<a href="#">3D Model</a>	<a href="#">Application Specification AS-171320-992-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification PK-78888-085-001 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">Product Specification PS-171320-999-001 (PDF)</a>	<a href="#">Symbol Footprint Data SYM-171320-1022-001 (PDF)</a>
<a href="#">Application Specification AS-171320-990-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Application Specification AS-171320-991-001 (PDF)</a>	

**General**


Product Family	Backplane Connectors
Series	<a href="#">171320</a>
Application	Coplanar, Daughtercard
Application Tooling Documents	TM-622018899-001
Component Type	PCB Receptacle
Overview	<a href="#">Impel and Impel Plus Backplane Solutions</a>
Product Name	Impel
UPC	889056021579

**Physical**

Circuits (Loaded)	96
Circuits (maximum)	96
Color - Resin	Black
Durability (mating cycles max)	200
First Mate / Last Break	No
Guide to Mating Part	No
Keying to Mating Part	None
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	27.951/g
Number of Columns	12
Number of Pairs	4
Number of Rows	8
Orientation	Right Angle
PC Tail Length	1.30mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.00mm
Packaging Type	Tray
Pitch - Mating Interface	1.90mm
Pitch - Termination Interface	1.90mm
Plating min - Mating	0.762µm
Temperature Range - Operating	-55° to +85°C

**Electrical**

Current - Maximum per Contact	0.75A
Data Rate	40.0 Gbps
Impedance	90Ω
Shield Type	Full Shield
Voltage - Maximum	29.9V AC (RMS)/DC



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[171320 Series](#)

**Mates With**

Impel Vertical Backplane Header  
[1713151207](#) , [1713151238](#) , [1713151218](#)

**Solder Process Data**

Lead-free Process Capability

N/A

**Material Info****Reference - Drawing Numbers**

Application Specification	AS-171320-990-001, AS-171320-991-001, AS-171320-992-001
Electrical Model Document	1713202061REVA-000
Packaging Specification	PK-78888-085-001
Product Specification	PS-171320-999-001
S-Parameter Model	1713201218-000, 1713202061-000
Sales Drawing	SD-171320-0001-001
Symbol/Footprint Data	SYM-171320-1022-001

This document was generated on 10/04/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[171320-1022](#)