

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1552209010](#)

Status: **Active**

Overview: Flamar Standard and Custom Cables for Industrial Automation


Description: Flamar Distribution Box Cable, WSOR Jacket, Unshielded, 9 Circuits, 3x(0.75mm²) with Green-Yellow Ground + 6x(0.34mm²) / 3x(19 AWG) with Green-Yellow Ground + 6x(22 AWG), 8.50mm (.335") Diameter, 200.0m (656.17') Length, Grey

Documents:

[Product Specification 1552209001-P1E \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

[Brochure \(PDF\)](#)



General

Product Family	Cable
Series	155220
Crimp Quality Equipment	Yes
Geographic Area	Global
Overview	<u>Flamar Standard and Custom Cables for Industrial Automation</u>
Product Name	Flamar, Signal and Control
UPC	889056463287

Physical

Bending Radius - Minimum	> 10xOD
Cable Length	200.0m
Circuits (Loaded)	9 (3+6)
Color - Cable Jacket	Gray
Insulation	TPE
Material - Outer Jacket	WSOR
Net Weight	0.010/g
Outer Jacket Diameter	8.50mm
Packaging Type	Reel
Temperature Range - Operating	-25° to +80°C
Wire Size AWG	19, 22
Wire Size mm ²	0.34, 0.75
Wire/Cable Type	UL AWM 21215 / CSA

Electrical

Current - Maximum per Contact	Contact Molex
Voltage - Maximum	600V

Material Info

Engineering Number	1X200M
--------------------	--------

Reference - Drawing Numbers

Product Specification	1552209001-P1E
-----------------------	----------------

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS Not Reviewed

ELV Not Reviewed

RoHS Phthalates Not Reviewed

China RoHS

Search Parts in this Series

[155220](#) Series

Use With

Brad M23 [120230](#) , [120233](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[155220-9010](#)