


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1718564012](#)  
**Status:** **Active**  
**Overview:** [KK Interconnect Solutions](#)  
**Description:** 2.54mm Pitch, KK 254 RPC Vertical Header with Friction Lock, 15µm Gold (Au) Plating, Pin Length 12.95mm, Tape and Reel, 12 Circuits

**Documents:**

<a href="#">3D Model (PDF)</a>	<a href="#">Product Specification PS-171856-0002-001 (PDF)</a>
<a href="#">3D Model</a>	<a href="#">Packaging Specification PK-171856-0001-000 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Symbol Footprint Data SYM-171856-0012-001 (PDF)</a>
<a href="#">Product Specification PS-171856-0001-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>



**Agency Certification**

UL E29179

**General**

Product Family	PCB Headers
Series	<a href="#">171856</a>
Application	Board-to-Board, Power, Signal, Wire-to-Board
Comments	See Product Specification for maximum current rating by AWG.  See Product Specification for operating temperature range by material.
Overview	<a href="#">KK Interconnect Solutions</a>
Product Name	KK 254
UPC	887191573120

**Physical**

Breakaway	No
Circuits (Loaded)	12
Circuits (maximum)	12
Color - Resin	Black
Durability (mating cycles max)	25
First Mate / Last Break	No
Flammability	94V-1
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Matte Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	1.378/g
Number of Rows	1
Orientation	Vertical
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	2.54mm
Plating min - Mating	0.381µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Robotic Placement	Pick and Place Cap
Shrouded	Partial
Stackable	No
Surface Mount Compatible (SMC)	Yes

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[171856](#) Series

**Mates With**

[4455](#) , [2695](#) , [6471](#)

Temperature Range - Operating -40° to +105°C, -40° to +80°C  
Termination Interface: Style Through Hole

**Electrical**

Current - Maximum per Contact 4.0A  
Voltage - Maximum 500V

**Solder Process Data**

Duration at Max. Process Temperature (seconds) 030  
Lead-free Process Capability SMC&WAVE  
Max. Cycles at Max. Process Temperature 003  
Process Temperature max. C 260

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification PK-171856-0001-000  
Product Specification PS-171856-0001-001, PS-171856-0002-001  
Sales Drawing SD-171856-0001-000  
Symbol/Footprint Data SYM-171856-0012-001

This document was generated on 10/05/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[171856-4012](#)