

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1552410028](#)

Status: **Active**

Overview: [Flamar Standard and Custom Cables for Industrial Automation](#)

Description: Flamar Sensor Cable, TPE Jacket, Braided Shielding Overall, 5 Circuits, 0.34mm² / 22 AWG, 6.40mm (.252") Diameter, 300.0m (984.25') Length, Gray

Documents:

[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable
Series	155241
Comments	3 reels of 100.0m each
Crimp Quality Equipment	Yes
Geographic Area	Global
Overview	Flamar Standard and Custom Cables for Industrial Automation
Product Name	Flamar, Signal and Control
UPC	889056458948

Physical


Bending Radius - Minimum	> 10xOD
Cable Length	300.0m
Circuits (Loaded)	5
Color - Cable Jacket	Gray
Insulation	PVC
Material - Outer Jacket	TPE
Net Weight	0.010/g
Outer Jacket Diameter	6.40mm
Packaging Type	Reel
Temperature Range - Operating	-40° to +105°C
Wire Size AWG	22
Wire Size mm ²	0.34
Wire/Cable Type	UL Listed PLTC

Electrical

Current - Maximum per Contact	Contact Molex
Voltage - Maximum	300V

Material Info

Engineering Number	3X100M
--------------------	--------



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[155241 Series](#)

Use With

Nano-Change (M8) [120091](#) , Micro-Change (M12) [120071](#) , Ultra-Lock (M12) [120085](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[155241-0028](#)