

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1553319010](#)

Status: **Active**

Overview: [Flamar Standard and Custom Cables for Industrial Automation](#)

Description: Flamar Feedback Cable, PUR Jacket, Braided Shielding Overall, 16 Circuits, 3x(2x0.14mm² with Spiral Shield) + 2x(0.50mm²) + 4x(0.14mm²) + 4x(0.25mm²) / 3x(2x26 AWG with Spiral Shield) + 2x(21 AWG) + 4x(26 AWG) + 4x(24 AWG), 10.00mm (.394") Diameter, 100.0m (328.08') Length, Green

Documents:

[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable
Series	155331
Crimp Quality Equipment	Yes
Geographic Area	Global
Overview	Flamar Standard and Custom Cables for Industrial Automation
Product Name	Flamar, Servo Motor
UPC	889056462167

Physical

Bending Radius - Minimum	> 10xOD
Cable Length	100.0m
Circuits (Loaded)	16 (6+2+4+4)
Color - Cable Jacket	Green
Insulation	TPE
Material - Outer Jacket	PUR
Net Weight	0.010/g
Outer Jacket Diameter	10.00mm
Packaging Type	Reel
Temperature Range - Operating	-40° to +80°C
Wire Size AWG	21, 24, 26
Wire Size mm ²	0.14, 0.22, 0.50
Wire/Cable Type	UL AWM 21223 / CSA

Electrical

Current - Maximum per Contact	Contact Molex
Voltage - Maximum	1000V

Material Info

Engineering Number	1X100M
--------------------	--------



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS Not Reviewed

ELV Not Reviewed

RoHS Phthalates Not Reviewed

Search Parts in this Series

[155331](#) Series

Use With

Brad M23 [120230](#) , [120233](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[155331-9010](#)