

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1554116005](#)

**Status:** **Active**

**Overview:** [Flamar Standard and Custom Cables for Industrial Automation](#)

**Description:** Flamar Ethernet 5e Network Cable, PVC Jacket, Braided Shielding Overall, 8 Circuits, 4x(2x0.14mm<sup>2</sup>) / 4x(2x26 AWG), 7.20mm (.283") Diameter, 500.0m (1640.42') Length, Teal

**Documents:**

[Brochure \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Cable
Series	<a href="#">155411</a>
Crimp Quality Equipment	Yes
Geographic Area	Global
Overview	<a href="#">Flamar Standard and Custom Cables for Industrial Automation</a>
Product Name	Flamar, Network
Protocol	EtherNet 5e
UPC	889056463539

**Physical**

Bending Radius - Minimum	> 15xOD
Cable Length	500.0m
Circuits (Loaded)	8
Color - Cable Jacket	Teal
Insulation	PE
Material - Outer Jacket	PVC
Net Weight	0.010/g
Outer Jacket Diameter	7.20mm
Packaging Type	Reel
Temperature Range - Operating	+5° to +60°C
Wire Size AWG	26
Wire Size mm <sup>2</sup>	0.14
Wire/Cable Type	UL AWM 2464 / CSA

**Electrical**

Current - Maximum per Contact	Contact Molex
Voltage - Maximum	300V

**Material Info**

Engineering Number	1X500M
--------------------	--------



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS Not Reviewed

ELV Not Reviewed

RoHS Phthalates Not Reviewed

**China RoHS**

**Search Parts in this Series**

[155411](#) Series

**Use With**

Micro-Change (M12) [130047](#) , [120100](#) , [130034](#) , [120071](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[155411-6005](#)