


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1718564004](#)
Status: **Active**
Overview: [KK Interconnect Solutions](#)
Description: 2.54mm Pitch, KK 254 RPC Vertical Header with Friction Lock, 15µm Gold (Au) Plating, Pin Length 12.95mm, Tape and Reel, 4 Circuits

Documents:

3D Model	Product Specification PS-171856-0002-001 (PDF)
3D Model (PDF)	Packaging Specification PK-171856-0001-000 (PDF)
Drawing (PDF)	Symbol Footprint Data SYM-171856-0004-001 (PDF)
Product Specification PS-171856-0001-001 (PDF)	RoHS Certificate of Compliance (PDF)



Agency Certification

UL E29179

General

Product Family	PCB Headers
Series	171856
Application	Board-to-Board, Power, Signal, Wire-to-Board
Comments	See Product Specification for maximum current rating by AWG. See Product Specification for operating temperature range by material.
Overview	KK Interconnect Solutions
Product Name	KK 254
UPC	887191572369

Physical

Breakaway	No
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Black
Durability (mating cycles max)	25
First Mate / Last Break	No
Flammability	94V-1
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Matte Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	0.449/g
Number of Rows	1
Orientation	Vertical
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	2.54mm
Plating min - Mating	0.381µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Robotic Placement	Pick and Place Cap
Shrouded	Partial
Stackable	No
Surface Mount Compatible (SMC)	Yes

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[171856 Series](#)

Mates With

[4455](#) , [2695](#) , [6471](#)

Temperature Range - Operating -40° to +105°C, -40° to +80°C
Termination Interface: Style Through Hole

Electrical

Current - Maximum per Contact 4.0A
Voltage - Maximum 500V

Solder Process Data

Duration at Max. Process Temperature (seconds) 030
Lead-free Process Capability SMC&WAVE
Max. Cycles at Max. Process Temperature 003
Process Temperature max. C 260

Material Info

Reference - Drawing Numbers

Packaging Specification PK-171856-0001-000
Product Specification PS-171856-0001-001, PS-171856-0002-001
Sales Drawing SD-171856-0001-000
Symbol/Footprint Data SYM-171856-0004-001

This document was generated on 10/05/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[171856-4004](#)