

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2016060680](#)
Status: **Active**
Overview: [High-Current, Universal-Clamp Terminal Blocks](#)
Description: High Current Universal Clamp Tapping Terminal Block, 35.00mm DIN-rail or Screw Mount, 285.0A / 600V, Grey Housing and Cover, 1 Circuit, 4 Terminations

Documents:

3D Model	RoHS Certificate of Compliance (PDF)
Drawing (PDF)	Product Literature (PDF)
3D Model (PDF)	

Agency Certification

UL E48521

General

Product Family	Terminal Blocks
Series	201606
Application	Wire-to-Wire
Component Type	One Piece
Overview	High-Current, Universal-Clamp Terminal Blocks
Product Name	Universal Clamp
Type	Universal Clamp
UPC	78172551153

Physical

Circuits (Loaded)	1
Circuits (maximum)	1
Color - Resin	Grey
Entry Angle	Horizontal
Lock to Mating Part	None
Material - Metal	Aluminum
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyamide
Number of Rows	2
Orientation	Vertical
Panel Mount	Screws
Pitch - Mating Interface	N/A
Polarized to Mating Part	N/A
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Screw
Wire Size AWG	1/0+1/0, 2+2, 2+2+2, 300 MCM-2
Wire Size mm ²	33.60+33.60, 33.60+33.60+33.60, 33.60-152.01, 53.00+53.00

Electrical


Current - Maximum per Contact	285.0A
Voltage - Maximum	600V

Material Info

Engineering Number MX-KE68

Reference - Drawing Numbers

Sales Drawing 2016060680-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[201606 Series](#)

This document was generated on 08/25/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[201606-0680](#)