

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1728790209

Status:

Active

Overview:


EdgeMate Wire-to-Edge-Card Power Connector

Description:

3.96mm Pitch EdgeMate Wire-to-Board Edge Card Connector, Female, Nylon 6, Black, UL94-V2, without Lock, Glow-Wire Capable, 9 Circuits

Replacement Part Number :

http://www.molex.com/molex/search/partSearch?pQuery=&sType=p&query=17215906091721590609



Series image - Reference only

Documents:

Drawing (PDF)

Product Specification PS-172160-0001-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E29179
Application tooling part link	
Application Tooling Part Link	11-03-0016
General	
Product Family	Edge Card Connectors
Series	172879
Comments	See Product Specification for maximum current rating by wire AWG and terminal material.
Component Type	Edgecard to Wire
Data Rate	Unrated
Edge Card Thickness	N/A
High Power Bay (30.0A or more)	No
Orientation	Right-Angle
Overview	EdgeMate Wire-to-Edge-Card Power Connector
Product Name	EdgeMate
Replacement Part Number	1721590609
Replacement Part Number	Non glow-wire
Standard Based	General
UPC	889056377119
Physical	
(p)ower-(s)ignal Configuration	9p - 0s
Circuit Size Range	1-64 Circuits
Circuits (Loaded)	9
Circuits (maximum)	9
Color - Resin	Black
Durability (mating cycles max)	25
Entry Angle	90° Angle
Flammability	94V-2
Keying to Mating Part	Yes
Material - Plating Mating	N/A
Material - Resin	Nylon
Net Weight	3.493/g
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.57mm
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.96mm
Polarized to Mating Part	Polarizing Ribs
Temperature Range - Operating	-40° to +105°C, -40° to +80°C
Termination Interface: Style	Straddle Mount-Edge Card

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)9139-DC (19 Jan 2021)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

172879 Series

Mates With

Edge Card PCB

Use With

172160

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Extraction Tool for Flat Blade, 3.96mm KK, 2.00mm, 3.96mm EdgeMate, and Ultra-Fit Terminals	11030016

Electrical

Current - Maximum per Contact	7.0A
Voltage - Maximum	250V

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Reference - Drawing Numbers

Product Specification	PS-172160-0001-001
Sales Drawing	SD-172879-0000-000

This document was generated on 02/19/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[172879-0209](#)