

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [2451320430](#)  
**Status:** **Active**  
**Overview:**  
**Description:** Micro-fit 3.0-to-Micro-Fit 3.0 Off-the-Shelf (OTS) Overmolded Cable Assembly, Dual Row, 3.0m Length, 4 Circuits, Black

**General**

Product Family	Cable Assemblies
Series	<a href="#">245132</a>
Application	Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Micro-Fit 3.0 Both Ends
Overmolded	Yes
Overview	microfit_30
Product Name	Micro-Fit 3.0
Type	Overmolded Assembly
UPC	889056862158

**Physical**

Cable Length	3.0m
Circuits (Loaded)	4
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	159.132/g
Number of Rows	2
Packaging Type	Bag
Pitch - Mating Interface	3.00mm
Plating min - Mating	1.016µm
Plating min - Termination	1.016µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	5.50mm
Wire Size AWG	20
Wire/Cable Type	UL 2464

**Electrical**

Current - Maximum per Contact	5.6A
Voltage - Maximum	300V AC

**Material Info**

Engineering Number	795161043
--------------------	-----------

**Reference - Drawing Numbers**

Packaging Specification	245132043-PK
Sales Drawing	2014400088-000

**EU ELV**  
**Compliant**

**EU RoHS**  
**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)9139-DC (19  
Jan 2021)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Compliant

Not Contained

**Search Parts in this Series**

[245132](#) Series

**Mates With**

Micro-Fit 3.0 Plug Housings [43020](#)  
<br>Micro-Fit 3.0 Headers [43045](#) <br>Micro-Fit 3.0 Test Plug [44242](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[245132-0430](#)