


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [2451360420](#)
Status: **Active**
Overview: [Mega-Fit Power Connectors](#)
Description: Mega-Fit-to-Mega-Fit Off-the-Shelf (OTS) Overmolded Cable Assembly, Dual Row, 2.0m Length, Gold (Au) Plated, 4 Circuits, Black

Documents:

3D Model	Packaging Specification 2027040011-PK (PDF)
3D Model (PDF)	Datasheet (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)



General

Product Family	Cable Assemblies
Series	245136
Application	Power, Wire-to-Board
Assembly Configuration	Dual Ended Connectors
Connector to Connector	Mega-Fit-to-Mega-Fit
Overmolded	Yes
Overview	Mega-Fit Power Connectors
Product Name	Mega-Fit
Type	Overmolded Assembly
UPC	889056878197

Physical

Cable Length	2.0m
Circuits (Loaded)	4
Color - Resin	Black
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Matte Tin
Material - Resin	PBT
Net Weight	401.000/g
Number of Rows	2
Packaging Type	Bag
Pitch - Mating Interface	5.70mm
Plating min - Mating	0.381µm
Plating min - Termination	0.381µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	10.30mm
Wire Size AWG	12
Wire/Cable Type	UL 2464

Electrical

Current - Maximum per Contact	15.0A
Voltage - Maximum	300V AC

Material Info

Reference - Drawing Numbers

Packaging Specification	2027040011-PK
Sales Drawing	2014400071-000

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[245136 Series](#)

Mates With

Mega-Fit Header [172064](#) , [172065](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[245136-0420](#)