

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0330122002](#)  
**Status:** **Active**  
**Overview:** [MX150 Sealed and Unsealed Connector System](#)  
**Description:** [MX150 Female Terminal for Mat-Sealed Connectors, Tin Plating, 18 and 20 AWG, Right Reel Payoff](#)

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Application Specification AS-33012-002-FR-001 (PDF)</a>
<a href="#">Product Specification PS-33012-002-001 (PDF)</a>	<a href="#">Packaging Specification 313025040-000 (PDF)</a>
<a href="#">Application Specification 330120000-AS-KR-000 (PDF)</a>	<a href="#">Test Summary TS-33012-002-001 (PDF)</a>
<a href="#">Application Specification AS-33012-002-001 (PDF)</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">Application Specification AS-33012-002-CH-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**General**

Product Family	Crimp Terminals
Series	33012
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	For automatic and semi-automatic crimping, use Left Reel Payoff terminals. See Sales Drawing for Left Reel Payoff Part Numbers.

**Crimp Quality Equipment**

Overview	Yes
Product Name	<a href="#">MX150 Sealed and Unsealed Connector System</a>
UPC	MX150 822350084239

**Physical**

Gender	Female
Grip Code	18
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.391/g
Packaging Type	Reel
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	2.54mm max.
Wire Size AWG	18, 20
Wire Size mm <sup>2</sup>	0.75-1.00

**Electrical**

Current - Maximum per Contact	Contact Molex
Voltage - Maximum	14V DC

**Solder Process Data**

Lead-free Process Capability	N/A
------------------------------	-----

**Material Info**

**Reference - Drawing Numbers**

Application Specification	330120000-AS-KR-000, AS-33012-002-001, AS-33012-002-CH-001, AS-33012-002-FR-001
Packaging Specification	313025040-000
Product Specification	PS-33012-002-001
Sales Drawing	SD-33012-002-001



Series image - Reference only

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Compliant

Not Contained

**Search Parts in this Series**

33012 Series

**Use With**

[33472](#) Dual Row Housing, [33476](#) Hybrid Housing, [33471](#) Single Row Housing

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

Extraction Toolkit for MX150 Connectors PremiumGrade Hand Crimp Tool for MX150 Female Terminals, 18-22 AWG	<a href="#">2002220700</a> <a href="#">638116000</a>
PremiumGrade Hand Crimp Tool for MX150 Female	<a href="#">638116100</a>

Terminals for  
1.00mm<sup>2</sup> and  
1.50mm<sup>2</sup> Metric  
Wires  
Hand Crimp Tool [638116200](#)  
Metric 0.5 and 0.75  
Extraction Tool for [638131500](#)  
MX150L, MX150, PT  
Bulb Socket, iGrid,  
SPOX, and Wire-to-  
Motor Terminals  
ServiceGrade [640160133](#)  
Hand Crimp Tool  
for MX150 Crimp  
Terminals, 14-22  
AWG

This document was generated on 02/07/2022

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[33012-2002](#)