

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0754330105**  
**Status:** **Active**  
**Overview:** GbX Backplane Connector System  
**Description:** GbX 3 Pair Backplane Connector System, Open Header, 60 Circuits, 10 Columns, Gold (Au) 0.76µm, Pin Length 5.55mm

**Documents:**

[3D Model](#) [Packaging Specification PK-70873-576 \(PDF\)](#)  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-75221-999-001 \(PDF\)](#)

**Agency Certification**


UL E29179

**General**

Product Family Backplane Connectors  
Series [75433](#)  
Application Backplane  
Application Tooling Documents TM-622022099  
Comments Open Header, Open Header  
Component Type PCB Header  
Overview [GbX Backplane Connector System](#)  
Product Name GbX  
UPC 822350145466

**Physical**

Circuits (Loaded) 60  
Circuits (maximum) 60  
Color - Resin Black  
Durability (mating cycles max) 200  
First Mate / Last Break No  
Flammability 94V-0  
Guide to Mating Part No  
Keying to Mating Part None  
Material - Metal High Performance Alloy (HPA)  
Material - Plating Mating Gold  
Material - Plating Termination Tin-Lead  
Material - Resin High Temperature Thermoplastic  
Net Weight 3.384/g  
Number of Columns 10  
Number of Pairs 3  
Number of Rows 6  
Orientation Vertical  
PC Tail Length 2.20mm  
PCB Locator No  
PCB Retention Yes  
PCB Thickness - Recommended 1.60mm  
Packaging Type Tube  
Pitch - Mating Interface 1.85mm  
Pitch - Termination Interface 1.85mm  
Plating min - Mating 0.762µm  
Plating min - Termination 0.762µm  
Polarized to PCB No  
Stackable Yes  
Surface Mount Compatible (SMC) Yes  
Temperature Range - Operating 105°C  
Termination Interface: Style Through Hole - Compliant Pin



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
ED/71/2019 (16 July  
2019)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[75433](#) Series

**Mates With**

[75370](#) GbX Daughtercards

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
Single Pin Repair Tool	<a href="#">622022090</a>
Shield Removal Tool	<a href="#">622022100</a>
3-Pair by 10-Wide Differential Insertion Tool	<a href="#">622022510</a>

**Electrical**

Current - Maximum per Contact	1.0A
Data Rate	8.0 Gbps
Real Signals (per 25mm)	81
Shield Type	Ground Plane Shield
Shielded	Yes
Voltage - Maximum	120V AC (RMS)/DC

**Solder Process Data**

Lead-free Process Capability	N/A
------------------------------	-----

**Material Info****Reference - Drawing Numbers**

Packaging Specification	PK-70873-576
Product Specification	PS-75221-999-001
Sales Drawing	SD-75433-010

This document was generated on 09/16/2019

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[75433-0105](#)