

6525 MHz SMD Dielectric Filter



AFII-DF-0037

Request Samples



Check Inventory



9.4 x 4.1 x 3.0 mm
RoHS Compliant
MSL Level = N/A



Features

- Bandpass Dielectric Filter with 1200 MHz bandwidth
- Surface Mount 9.4 x 4.1 x 3.0 mm package
- Single-Ended Input and Output
- Excellent selectivity with high out-of-band rejection
- RoHS Compliant

Applications

- WiFi 6E/7 Access Points and Routers
- Industrial IoT
- Enterprise Networks
- 6 GHz (U-NII-5 / U-NII-6 / U-NII-7 / U-NII-8)

Product Image



6525 MHz SMD Dielectric Filter



AFII-DF-0037

Request Samples



Check Inventory



9.4 x 4.1 x 3.0 mm

RoHS Compliant

MSL Level = N/A

Electrical Specification

Parameters	Minimum	Typical	Maximum	Units	Notes
Center Frequency (fc)	-	6525.0	-	MHz	
Bandwidth	-	1200	-	MHz	5925 – 7125 MHz
Insertion Loss	-	1.05	3.5	dB	5925 – 7125 MHz @25°C
			4.0	dB	5925 – 7125 MHz @-40°C ~ +105°C
VSWR	≤ 2.0				5925 – 7125 MHz
Amplitude Ripple	-	-	3.0	dB _{p-p}	5925 – 7125 MHz
Attenuation	50	-	-	dB	0 ~ 5640 MHz
	45			dB	5640 ~ 5835 MHz
Input Power			3	W	
Source Impedance ⁽¹⁾ (single ended)	-	50	-	Ω	
Load Impedance ⁽¹⁾ (single ended)	-	50	-	Ω	

Notes: (1) No matching network needed (Ref. Testing Environment Circuit as shown in “Measurement Circuit” section).

Mechanical Specification

Parameters	Specifications
Dimension	9.4 x 4.1 x 3.0 mm
Mounting Type	SMD Mount

Environmental Specification

Parameters	Specifications
Operating Temperature Range	-40°C ~ +105°C
Storage Temperature Range	-40°C ~ +105°C
RoHS Compliant	Yes

Ordering Information

Part Number	Description
AFII-DF-0037	6525 MHz SMD Dielectric Filter
AFII-DF-0037-EVB	6525 MHz SMD Dielectric Filter Evaluation Board



5101 Hidden Creek Ln Spicewood TX 78669
Phone: 512-371-6159 | Fax: 512-351-8858
For terms and conditions of sales, please visit:
www.abracon.com

REVISED: 09-09-24

ABRACON IS
ISO9001-2015
CERTIFIED

6525 MHz SMD Dielectric Filter



AFII-DF-0037

Request Samples




Check Inventory




9.4 x 4.1 x 3.0 mm
RoHS Compliant
MSL Level = N/A

Product Dimensions


TOP VIEW



SIDE VIEW



BOTTOM VIEW



TOLERANCE : ± 0.20

UNIT: mm

*:MONTH CODE

Unit : mm

6525 MHz SMD Dielectric Filter



AFII-DF-0037

Request Samples



Check Inventory




9.4 x 4.1 x 3.0 mm

RoHS Compliant


MSL Level = N/A

PCB Footprint & EVB

Please reach out to us for more detailed layout info via [Abracon online support](#)



Unit : mm



Unit : mm

6525 MHz SMD Dielectric Filter



AFII-DF-0037

Request Samples



Check Inventory





9.4 x 4.1 x 3.0 mm

RoHS Compliant

MSL Level = N/A

Measurement Circuit



6525 MHz SMD Dielectric Filter



AFII-DF-0037

Request Samples




Check Inventory




9.4 x 4.1 x 3.0 mm
RoHS Compliant
MSL Level = N/A

Frequency Characteristics

S21 narrow band



S21 wide band



6525 MHz SMD Dielectric Filter



AFII-DF-0037

Request Samples




Check Inventory



9.4 x 4.1 x 3.0 mm
RoHS Compliant
MSL Level = N/A

Group Delay Ripple



6525 MHz SMD Dielectric Filter



AFII-DF-0037

Request Samples





Check Inventory



9.4 x 4.1 x 3.0 mm
RoHS Compliant
MSL Level = N/A

VSWR (S11 & S22)



6525 MHz SMD Dielectric Filter



AFII-DF-0037

Request Samples




Check Inventory




9.4 x 4.1 x 3.0 mm
RoHS Compliant
MSL Level = N/A

Smith Chart (S11 & S22)

Smith chart S11 (5925~7125MHz)



Smith chart S22 (5925~7125MHz)



6525 MHz SMD Dielectric Filter



AFII-DF-0037

Request Samples



Check Inventory



9.4 x 4.1 x 3.0 mm
RoHS Compliant
MSL Level = N/A

Reflow Profile [JEDEC J-STD-020]

Solder Paste: Ag3.0/Cu0.5/Sn




Table 1

SnPb Eutectic Process

Classification Temperatures (T_c)

Package Thickness	Volume mm ³ <350	Volume mm ³ ≥ 350
<2.5mm	235°C	220°C
≥ 2.5mm	220°C	220°C

Table 2

Pb-Free Process

Classification Temperatures (T_c)

Package Thickness	Volume mm ³ <350	Volume mm ³ 350-2000	Volume mm ³ >2000
<1.6mm	260°C	260°C	260°C
1.6mm - 2.5mm	260°C	250°C	245°C
>2.5mm	240°C	240°C	240°C

Profile Feature	Sn-Pb Eutectic Assembly	Pb-Free Assembly
Preheat / soak		
Temperature minimum (T_{smin})	100°C	150°C
Temperature maximum (T_{smax})	150°C	200°C
Time (T_{smin} to T_{smax}) (t_s)	60 – 120 sec.	60 – 120 sec.
Average ramp-up rate (T_{smax} to T_p)	3°C/sec. max	3°C/sec. max
Liquidous temperature (T_L)	183°C	220°C
Time at Liquidous (T_L)	60 – 150 sec.	30 – 100 sec.
Peak package body temperature (T_p)*	See Table 1	See Table 2
Time (T_p)** within 5°C of the specified classification temperature (T_c)	20 sec.	5 sec.
Ramp-down rate (T_p to T_{smax})	6°C/sec. max	2-6°C/sec. max
Time 25°C to peak temperature	6 min. max	8 min. max
Reflow cycles	2 max	2 max

*Tolerance for peak profile temperature (T_p) is defined as a supplier minimum and a user maximum.

**Tolerance for time at peak profile temperature (t_p) is defined as a supplier minimum and a user maximum.

9.4 x 4.1 x 3.0 mm
RoHS Compliant
MSL Level = N/A

Tape & Reel Dimension



E ₁	P ₀	F	P ₁	P ₂	D ₀	W	A ₀	B ₀	K ₀	Reel Qty
1.75±0.1	4.0±0.1	11.5±0.1	12.0±0.1	2.0±0.1	1.5±0.1	24.0±0.2	4.7±0.1	10.0±0.2	3.3±0.1	1,500

A	B	W_1	N	C
330 ± 3	2.0 ± 0.5	26max	80min	13 ± 0.5



ABRACON IS
ISO9001-2015
CERTIFIED

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ABRACON:](#)

[AFII-DF-0037](#)