

AFM912N

Airfast RF Power LDMOS Transistor

Rev. 0 — November 2022

Data Sheet: Technical Data

Designed for handheld two-way radio applications with frequencies from 136 to 941 MHz. The high gain, ruggedness and wideband performance of this device make it ideal for large-signal, common-source amplifier applications in handheld radio equipment.

Typical Performance (7.5 Vdc, $T_A = 25^\circ\text{C}$, CW)

| Frequency (MHz) | Gain Compression | P_{out} (W) | G_{ps} (dB) | η_D (%) |
|-----------------|------------------|----------------------|----------------------|--------------|
| 941 | P1dB | 12.5 | 13.3 | 65.2 |
| | P3dB | 15.7 | 11.3 | 69.5 |

Load Mismatch/Ruggedness

| Frequency (MHz) | Signal Type | VSWR | P_{in} (dBm) | Test Voltage | Result |
|-----------------|-------------|----------------------------|-----------------------|--------------|-----------------------|
| 941 | CW | > 10:1 at all Phase Angles | 32.9 (3 dB Overdrive) | 10.0 | No Device Degradation |

Features

- Characterized for operation from 136 to 941 MHz
- Unmatched input and output allowing wide frequency range utilization
- Device can be used single-ended or in a push-pull configuration
- Integrated ESD protection
- Integrated stability enhancements
- Wideband — full power across each band
- Extreme ruggedness
- High linearity for: TETRA, SSB

Typical Applications


- Output stage VHF band handheld radio
- Output stage UHF band handheld radio
- Output stage for 700–800 MHz handheld radio

AFM912N

136–941 MHz, 12 W, 7.5 V
**WIDEBAND
AIRFAST RF POWER LDMOS
TRANSISTOR**



DFN 4 × 6



(Top View)

Note: Exposed backside of the package is the source terminal for the transistor.

Figure 1. Pin Connections

Table 1. Maximum Ratings

| Rating | Symbol | Value | Unit |
|--|-----------|-------------|-----------|
| Drain–Source Voltage | V_{DS} | –0.5, +30 | Vdc |
| Gate–Source Voltage | V_{GS} | –6.0, +12 | Vdc |
| Operating Voltage | V_{DD} | 0 to 12.5 | Vdc |
| Storage Temperature Range | T_{stg} | –65 to +150 | °C |
| Case Operating Temperature Range | T_C | –40 to +150 | °C |
| Operating Junction Temperature Range ⁽¹⁾ | T_J | –40 to +150 | °C |
| Total Device Dissipation @ $T_C = 25^\circ\text{C}$ Derate above 25°C | P_D | 142 1.14 | W W/°C |

Table 2. Thermal Characteristics

| Characteristic | Symbol | Value ⁽²⁾ | Unit |
|---|-----------------|----------------------|------|
| Thermal Resistance, Junction to Case Case Temperature 78°C , 12.6 W CW, 7.5 Vdc, $I_{DQ(A+B)} = 130\text{ mA}$, 941 MHz | $R_{\theta JC}$ | 0.88 | °C/W |

Table 3. ESD Protection Characteristics

| Test Methodology | Class |
|---------------------------------------|-------------------------|
| Human Body Model (per JS–001–2017) | Class 1C, passes 1000 V |
| Charge Device Model (per JS–002–2014) | Class C3, passes 1200 V |

Table 4. Moisture Sensitivity Level

| Test Methodology | Rating | Package Peak Temperature | Unit |
|--------------------------------------|--------|--------------------------|------|
| Per JESD22–A113, IPC/JEDEC J–STD–020 | 3 | 260 | °C |

Table 5. Electrical Characteristics ($T_A = 25^\circ\text{C}$ unless otherwise noted)

| Characteristic | Symbol | Min | Typ | Max | Unit |
|----------------|--------|-----|-----|-----|------|
|----------------|--------|-----|-----|-----|------|

Off Characteristics ⁽³⁾

| | | | | | |
|---|-----------|---|---|-----|-----------------|
| Zero Gate Voltage Drain Leakage Current ($V_{DS} = 30\text{ Vdc}$, $V_{GS} = 0\text{ Vdc}$) | I_{DSS} | — | — | 10 | μAdc |
| Gate–Source Leakage Current ($V_{GS} = 5\text{ Vdc}$, $V_{DS} = 0\text{ Vdc}$) | I_{GSS} | — | — | 500 | nAdc |

On Characteristics ⁽³⁾

| | | | | | |
|--|--------------|-----|------|------|-----|
| Gate Threshold Voltage ($V_{DS} = 10\text{ Vdc}$, $I_D = 78\text{ }\mu\text{Adc}$) | $V_{GS(th)}$ | 1.7 | 2.1 | 2.6 | Vdc |
| Drain–Source On–Voltage ($V_{GS} = 10\text{ Vdc}$, $I_D = 780\text{ mAdc}$) | $V_{DS(on)}$ | — | 0.11 | 0.15 | Vdc |
| Forward Transconductance ($V_{DS} = 7.5\text{ Vdc}$, $I_D = 4.7\text{ Adc}$) | g_{fs} | — | 4.4 | — | S |

1. Continuous use at maximum temperature will affect MTTF.

2. Refer to AN1955, *Thermal Measurement Methodology of RF Power Amplifiers*. Go to <http://www.nxp.com/RF> and search for AN1955.

3. Each side of device measured separately.

(continued)

Table 5. Electrical Characteristics ($T_A = 25^\circ\text{C}$ unless otherwise noted) (continued)

| Characteristic | Symbol | Min | Typ | Max | Unit |
|--|-----------|-----|------|-----|------|
| Dynamic Characteristics ⁽¹⁾ | | | | | |
| Reverse Transfer Capacitance ($V_{DS} = 7.5\text{ Vdc} \pm 30\text{ mV(rms)ac}$ @ 1 MHz, $V_{GS} = 0\text{ Vdc}$) | C_{rss} | — | 1.7 | — | pF |
| Output Capacitance ($V_{DS} = 7.5\text{ Vdc} \pm 30\text{ mV(rms)ac}$ @ 1 MHz, $V_{GS} = 0\text{ Vdc}$) | C_{oss} | — | 39.8 | — | pF |
| Input Capacitance ($V_{DS} = 7.5\text{ Vdc}$, $V_{GS} = 0\text{ Vdc} \pm 30\text{ mV(rms)ac}$ @ 1 MHz) | C_{iss} | — | 68.9 | — | pF |

Typical Performance (In NXP Test Fixture, 50 ohm system) $V_{DD} = 7.5\text{ Vdc}$, $I_{DQ(A+B)} = 130\text{ mA}$, $P_{out} = 12\text{ W}$, $f = 941\text{ MHz}$

| | | | | | |
|-------------------|----------|---|------|---|----|
| Power Gain | G_{ps} | — | 13.3 | — | dB |
| Drain Efficiency | η_D | — | 65.2 | — | % |
| Input Return Loss | IRL | — | -17 | — | dB |

Load Mismatch/Ruggedness (In NXP Test Fixture, 50 ohm system) $I_{DQ(A+B)} = 130\text{ mA}$


| Frequency (MHz) | Signal Type | VSWR | P_{in} (dBm) | Test Voltage, V_{DD} | Result |
|-----------------|-------------|----------------------------|--------------------------|------------------------|-----------------------|
| 941 | CW | > 10:1 at all Phase Angles | 32.9 (3 dB Overdrive) | 10.0 | No Device Degradation |

Table 6. Ordering Information

| Device | Tape and Reel Information | Package |
|-----------|--|-----------|
| AFM912NT1 | T1 Suffix = 1,000 Units, 16 mm Tape Width, 7-inch Reel | DFN 4 × 6 |


1. Each side of device measured separately.

Typical Characteristics



Note: Each side of device measured separately.

Figure 2. Capacitance versus Drain-Source Voltage



Note 1: Each side of device measured separately.

Note 2: MTTF value represents the total cumulative operating time under indicated test conditions.

Figure 3. MTTF versus Junction Temperature – CW

941 MHz Test Fixture — 3" × 5" (7.8 cm × 12.7 cm)




Table 7. AFM912N Test Fixture Component Designations and Values — 941 MHz

| Part | Description | Part Number | Manufacturer |
|--------------------|---|---------------------|--------------|
| B1, B2 | Long RF Bead | 2743021447 | Fair-Rite |
| B3, B4 | Short RF Bead | 2743019447 | Fair-Rite |
| C1 | 2 pF Chip Capacitor | 600F2R0BT250XT | ATC |
| C2, C3 | 8.2 pF Chip Capacitor | 600F8R2BT250XT | ATC |
| C4, C5 | 6.8 pF Chip Capacitor | 600F6R8BT250XT | ATC |
| C6, C7, C8, C9 | 9.1 pF Chip Capacitor | 600F9R1BT250XT | ATC |
| C10, C11 | 5.6 pF Chip Capacitor | 600F5R6BT250XT | ATC |
| C12, C13 | 150 pF Chip Capacitor | 600F151JT250XT | ATC |
| C14 | 3 pF Chip Capacitor | 600F3R0BT250XT | ATC |
| C15, C17, C19, C23 | 1 μ F Chip Capacitor | GRM32CR72A105KA35L | Murata |
| C16, C18, C22, C26 | 10 μ F Chip Capacitor | C3225X7S1H106M250AB | TDK |
| C20, C21, C24, C25 | 0.1 μ F Chip Capacitor | GRM32MR71H104JA01L | Murata |
| C27, C28 | 0.2 pF Chip Capacitor | 600F0R2BT250XT | ATC |
| C29 | 5.1 pF Chip Capacitor | 600F5R1BT250XT | ATC |
| L1, L2 | 8 nH Inductor, 3 Turns | A03TKLC | Coilcraft |
| L3, L4 | 5 nH Inductor, 2 Turns | A02TJLC | Coilcraft |
| R1, R2 | 100 Ω , 1/4 W Chip Resistor | CRCW1206100RFKEA | Vishay |
| R3, R4 | 3.3 Ω , 1/2 W Chip Resistor | ERJ-14YJ3R3U | Panasonic |
| PCB | Rogers RO4350B, 0.030", $\epsilon_r = 3.66$ | D84629 | MTL |

Typical Characteristics — 941 MHz Test Fixture




Figure 5. Output Power versus Gate-Source Voltage




Figure 6. Power Gain, Drain Efficiency and Output Power versus Input Power




Figure 7. Power Gain and Drain Efficiency versus Output Power over Temperature

941 MHz Test Fixture

| f (MHz) | $Z_{\text{source}}^{(1)}$ (Ω) | $Z_{\text{load}}^{(1)}$ (Ω) |
|------------|---|---|
| 941 | $0.4 - j1.7$ | $0.9 - j1.2$ |

1. Simulated data.

Z_{source} = Test circuit impedance as measured from gate to ground.

Z_{load} = Test circuit impedance as measured from drain to ground.





Figure 8. Series Equivalent Source and Load Impedance — 941 MHz




Figure 9. Product Marking

Package Information



| | | |
|---|---------------------------------|----------------------------|
| © NXP SEMICONDUCTORS N.V. ALL RIGHTS RESERVED | MECHANICAL OUTLINE | PRINT VERSION NOT TO SCALE |
| TITLE: DFN, THERMALLY ENHANCED 4 X 6 X 0.9, 0.8 & 0.65 PITCH, 16 TERMINAL | DOCUMENT NO: 98ASA00868D REV: B | |
| | STANDARD: NON-JEDEC | |
| | SOT1862-1 | 27 JUL 2016 |



| | | |
|---|--------------------------|----------------------------|
| © NXP SEMICONDUCTORS N.V. ALL RIGHTS RESERVED | MECHANICAL OUTLINE | PRINT VERSION NOT TO SCALE |
| TITLE: DFN, THERMALLY ENHANCED 4 X 6 X 0.9, 0.8 & 0.65 PITCH, 16 TERMINAL | DOCUMENT NO: 98ASA00868D | REV: B |
| | STANDARD: NON-JEDEC | |
| | SOT1862-1 | 27 JUL 2016 |

NOTES:

1. DIMENSIONING & TOLERANCING CONFIRM TO ASME Y14.5M-1994.
2. ALL DIMENSIONS ARE IN MILLIMETERS. ANGLES ARE IN DEGREES.
3. THIS DIMENSION APPLIES TO METALLIZED TERMINAL AND IS MEASURED BETWEEN 0.25 MM AND 0.30 MM FROM TERMINAL TIP.
4. COPLANARITY APPLIES TO THE EXPOSED HEAT SLUG AS WELL AS THE TERMINALS.

| | | |
|---|--------------------------------------|----------------------------|
| © NXP SEMICONDUCTORS N.V. ALL RIGHTS RESERVED | MECHANICAL OUTLINE | PRINT VERSION NOT TO SCALE |
| TITLE: DFN, THERMALLY ENHANCED 4 X 6 X 0.9, 0.8 & 0.65 PITCH, 16 TERMINAL | DOCUMENT NO: 98ASA00868D REV: B | |
| | STANDARD: NON-JEDEC | |
| | SOT1862-1 | 27 JUL 2016 |

Product Documentation, Software and Tools

Refer to the following resources to aid your design process.

Application Notes

- AN1907: Solder Reflow Attach Method for High Power RF Devices in Over-Molded Plastic Packages
- AN1955: Thermal Measurement Methodology of RF Power Amplifiers

Engineering Bulletins

- EB212: Using Data Sheet Impedances for RF LDMOS Devices

Software

- Electromigration MTTF Calculator

Development Tools

- Printed Circuit Boards

Revision History

The following table summarizes revisions to this document.

| Revision | Date | Description |
|----------|-----------|---|
| 0 | Nov. 2022 | <ul style="list-style-type: none">• Initial release of data sheet |

How to Reach Us

Home Page:
nxp.com

Web Support:
nxp.com/support

Information in this document is provided solely to enable system and software implementers to use NXP products. There are no express or implied copyright licenses granted hereunder to design or fabricate any integrated circuits based on the information in this document. NXP reserves the right to make changes without further notice to any products herein.

NXP makes no warranty, representation, or guarantee regarding the suitability of its products for any particular purpose, nor does NXP assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters that may be provided in NXP data sheets and/or specifications can and do vary in different applications, and actual performance may vary over time. All operating parameters, including "typicals," must be validated for each customer application by customer's technical experts. NXP does not convey any license under its patent rights nor the rights of others. NXP sells products pursuant to standard terms and conditions of sale, which can be found at the following address: nxp.com/SalesTermsandConditions.

NXP, the NXP logo, Freescale, the Freescale logo and Airfast are trademarks of NXP B.V. All other product or service names are the property of their respective owners.

© NXP B.V. 2022

All rights reserved.

For more information, please visit: <http://www.nxp.com>

For sales office addresses, please send an email to: salesaddresses@nxp.com

Date of release: November 2022
Document identifier: AFM912N

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

NXP:

[AFM912NT1](#)