


CU16025-UW2J

SIMPLIFIED DATASHEET

■ Features

16 character x 2 line display.
LCD compatible, serial
interface. Good for use as
LCD drop-in replacement, or
in various other applications.

■ Physical dimension



() Reference only
Unit:mm

Specifications

■ Electrical Ratings

Parameter	Symbol	Min.	Typ.	Max.	Unit	Condition
Logic Input Voltage						
DB0-DB7, RS,R/W(WR), E(RD),SCK, STB	VIH1	2.0	-	VCC	VDC	VCC-VSS= 5.0 V
	VIL1	VSS	-	0.8		
Logic Input Voltage	VIH2	0.7VCC	-	VCC	VDC	VCC-VSS= 5.0 V
SI/SO	VIL2	VSS	-	0.3VCC		
Logic Input Voltage	VIH3	0.8VCC	-	VCC	VDC	VCC-VSS= 5.0 V
/RESET	VIL3	VSS	-	0.2VCC		
Power supply Voltage	VCC-VSS	4.75	5.00	5.25	VDC	-

■ Physical Specifications

Parameter	*ANK(Alphabet, Numeric, Kana)
Number of char.	32 (16 x 2)
Built-in Fonts	5x7 ANK, International
Display area	51.4 x 11.4 mm (X x Y)
Character size	2.275 x 4.759 mm (X x Y)
	Underline is not included.
Character pitch	3.275 mm
Line pitch	5.991 mm
Weight	About 33 g

■ Electrical Characteristics

Parameter	Symbol	Min.	Typ.	Max.	Unit	Condition
Logic Output Voltage	'H'	VOH	VCC-0.8	-	VDC	IOH = -4 mA
	'L'	VOL	-	0.6		IOL = 4 mA
	'H'	VOH	VCC-0.5	-	VDC	IOH = -2 mA
	'L'	VOL	-	0.5		IOL = 2 mA
Power Supply Current 1	ICC1	-	150	200	mA	Display ON
Power Supply Current 2	ICC2	-	3	10	mA	Display OFF
Power Consumption		-	0.75	1.0	W	Display ON

■ Optical Characteristics

Parameter	
Luminance	350 cd/m ² Min.
Color of illumination	Green (Blue-Green)

■ Environmental Conditions

Parameter	
Operating Temperature	-40 ~ +85 degrees celsius
Storage Temperature	-50 ~ +85 degrees celsius
Operating Humidity	20 ~ 80% R.H. (non-condensing)
Vibration (Non operation)	10-55-10Hz, all amplitude 1mm, 30 minutes, X-Y-Z
Shock (Non operation)	539m/s ² (55G) 10ms

■ Interface

8bit/4bit Parallel(TTL), Synchronous Serial (CMOS)

■ Pin Assignment (Parallel)

Pin No.	Signal	Pin No.	Signal
1	GND	8	DB1
2	VCC	9	DB2
3	NC	10	DB3
4	RS	11	DB4
5	R/W(WR)	12	DB5
6	E(RD)	13	DB6
7	DB0	14	DB7

(Synchronous Serial)

Pin No.	Signal
1	VCC
2	SI/SO
3	GND
4	STB
5	SCK
6	NC

■ Functions

Parameter
Command compatible with HD44780 LCD controller
Display ON/OFF
Brightness Control
Cursor ON/OFF
8 User definable character font
etc.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Noritake:](#)

[CU16025-UW2J](#)