

AP821 20 Watts TO-220 High Power Resistors



A high power TO-220 style resistor package designed for high frequency emitter circuits in switching power supplies. Also used in voltage regulation and low energy pulse loading.

- 20 Watts at 25°C case temperature on heat sink
- Moulded case for protection and easy to mount
- Non-inductive design
- Electrically isolated case
- RoHS Compliant



Characteristics


Power rating:	2.25 Watts in free air
Operating voltage:	350V max
Dielectric strength:	1800Vac
Insulation resistance:	10GΩ min
Working temperature range:	-65°C to +150°C
Temperature coefficient:	As specified, referenced to 25°C, ΔR taken at +105°C
Overload:	ΔR ±0.3%, 2 times rated power with applied voltage not to exceed 1.5 times maximum continuous operating voltage for 5 seconds
Load life:	ΔR ±1.0%, 2000 hours at rated power
Damp heat with load:	ΔR ±0.5%, 40 ±2°C, 90 - 95% R.H max working voltage for 1000 hours with 1.5 hours "ON" and 0.5 hours "OFF"
Solderability:	90% min coverage, 245 ±5°C for 3 seconds
Thermal shock:	ΔR ±0.3%, -65°C - 150°C, 100 cycles
Terminal strength:	ΔR ±0.2%, 2.4 N
Vibration and high frequency:	ΔR ±0.2%, 20g peak

Electrical Specifications

Resistance Value Range	Available Tolerance & Pref. Value Ranges	Available TCR
R05 - 1R	J (±5%) K (±10%)	Not specified
1R02 - 3R	F (±1%) , J (±5%) , K (±10%)	±300ppm/°C
3R01 - 10R		±100ppm/°C ±200ppm/°C
10R2 - 10K	D (±0.5%) F (±1%) J (±5%) K (±10%)	±50ppm/°C ±100ppm/°C ±200ppm/°C

Preferred value ranges:
F (±1%) - E96 , J (±5%) - E24, K (±10%) - E12

Derating Curve



ARCOL UK Limited,
Threemilestone Ind. Estate,
Truro, Cornwall, TR4 9LG, UK.
T +44 (0) 1872 277431
F +44 (0) 1872 222002
E sales@arcolresistors.com

www.arcolresistors.com


The information contained herein does not form part of a contract and is subject to change without notice. ARCOL operate a policy of continual product development, therefore, specifications may change.

It is the responsibility of the customer to ensure that the component selected from our range is suitable for the intended application. If in doubt please ask ARCOL.

AP821 20 Watts TO-220 High Power Resistors



Dimensions (mm)



Ordering Procedure

Standard Resistor: Series, Resistance Value, Tolerance Code, TCR

eg: AP821 10K J ± 50 ppm/ $^{\circ}$ C

ARCOL UK Limited,
Threemilestone Ind. Estate,
Truro, Cornwall, TR4 9LG, UK.
T +44 (0) 1872 277431
F +44 (0) 1872 222002
E sales@arcolresistors.com

www.arcolresistors.com

The information contained herein does not form part of a contract and is subject to change without notice. ARCOL operate a policy of continual product development, therefore, specifications may change.

It is the responsibility of the customer to ensure that the component selected from our range is suitable for the intended application. If in doubt please ask ARCOL..

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Ohmite:

[AP821 3R3 J 100PPM](#) [AP821 1R F](#) [AP821 5K F 50PPM](#) [AP821 180R J 100PPM](#) [AP821 1R2 J](#) [AP821 2K7 F 50PPM](#) [AP821 15R J 100PPM](#) [AP821 R8 J](#) [AP821 56R F 50PPM](#) [AP821 4R7 F 100PPM](#) [AP821 1K2 J 100PPM](#) [AP821 180R F 50PPM](#) [AP821 27R F 50PPM](#) [AP821 39R J 100PPM](#) [AP821 150R F 50PPM](#) [AP821 150R J 100PPM](#) [AP821 1K5 F 50PPM](#) [AP821 4R7 J 100PPM](#) [AP821 100R J 100PPM](#) [AP821 680R F 50PPM](#) [AP821 R7 J](#) [AP821 1K J 100PPM](#) [AP821 R6 J](#) [AP821 2K2 J 100PPM](#) [AP821 3K9 F 50PPM](#) [AP821 33R F 50PPM](#) [AP821 15R F 50PPM](#) [AP821 2R5 F](#) [AP821 2K2 F 50PPM](#) [AP821 680R J 100PPM](#) [AP821 3K3 F 50PPM](#) [AP821 R1 J](#) [AP821 1K F 50PPM](#) [AP821 8R2 J 100PPM](#) [AP821 2R7 F](#) [AP821 1K8 F 50PPM](#) [AP821 25R J 100PPM](#) [AP821 R2 J](#) [AP821 R08 J](#) [AP821 1R5 J](#) [AP821 2R5 J](#) [AP821 68R J 100PPM](#) [AP821 820R J 100PPM](#) [AP821 2R2 J](#) [AP821 27R J 100PPM](#) [AP821 4K7 J 100PPM](#) [AP821 560R J 100PPM](#) [AP821 4K7 F 50PPM](#) [AP821 5K6 J 100PPM](#) [AP821 82R J 100PPM](#) [AP821 8K2 J 100PPM](#) [AP821 3R9 F 100PPM](#) [AP821 10R J 100PPM](#) [AP821 2R2 F](#) [AP821 R06 J](#) [AP821 50R F 50PPM](#) [AP821 220R F 50PPM](#) [AP821 390R J 100PPM](#) [AP821 25R F 50PPM](#) [AP821 330R J 100PPM](#) [AP821 270R F 50PPM](#) [AP821 18R F 50PPM](#) [AP821 2K5 J 100PPM](#) [AP821 2R7 J](#) [AP821 820R F 50PPM](#) [AP821 1R2 F](#) [AP821 2K5 F 50PPM](#) [AP821 1R8 J](#) [AP821 6K8 F 50PPM](#) [AP821 3K3 J 100PPM](#) [AP821 22R J 100PPM](#) [AP821 10R F 100PPM](#) [AP821 1K2 F 50PPM](#) [AP821 3R3 F 100PPM](#) [AP821 2K7 J 100PPM](#) [AP821 R05 J](#) [AP821 560R F 50PPM](#) [AP821 330R F 50PPM](#) [AP821 3R9 J 100PPM](#) [AP821 1R J](#) [AP821 R5 J](#) [AP821 120R F 50PPM](#) [AP821 5R6 J 100PPM](#) [AP821 270R J 100PPM](#) [AP821 6K8 J 100PPM](#) [AP821 68R F 50PPM](#) [AP821 1R8 F](#) [AP821 6R8 F 100PPM](#) [AP821 120R J 100PPM](#) [AP821 1R5 F](#) [AP821 390R F 50PPM](#) [AP821 8K2 F 50PPM](#) [AP821 R07 J](#) [AP821 5K J 100PPM](#) [AP821 82R F 50PPM](#) [AP821 1K8 J 100PPM](#) [AP821 5K6 F 50PPM](#) [AP821 5R F 100PPM](#) [AP821 10K J 100PPM](#) [AP821 50R J 100PPM](#)