


Bipolar Transistor

(-)160 V, (-)1.5 A, Low $V_{CE(sat)}$,
(PNP) NPN Single PCP

2SA1419, 2SC3649



1. Base
2. Collector
3. Emitter

SOT-89 / PCP-1
CASE 419AU

Features

- Adoption of FBET, MBIT Processes
- High Breakdown Voltage and Large Current Capacity
- Ultrasmall Size Making it Easy to Provide High-density, Small-sized Hybrid IC's

Specifications


(): 2SA1419

ABSOLUTE MAXIMUM RATINGS ($T_A = 25^\circ\text{C}$)


Symbol	Parameter	Conditions	Ratings	Unit
V_{CBO}	Collector-to-Base Voltage	-	(-)180	V
V_{CEO}	Collector-to-Emitter Voltage	-	(-)160	V
V_{EBO}	Emitter-to-Base Voltage	-	(-)6	V
I_C	Collector Current	-	(-)1.5	A
I_{CP}	Collector Current (Pulse)	-	(-)2.5	A
P_C	Collector Dissipation	-	500	mW
		When mounted on ceramic substrate (250 mm ² x 0.8 mm)	1.5	W
T_j	Junction Temperature	-	150	°C
T_{stg}	Storage Temperature	-	-55 to +150	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

ELECTRICAL CONNECTIONS



MARKING DIAGRAMS



AE/CE = Specific Device Code

ORDERING INFORMATION

See detailed ordering and shipping information on page 5 of this data sheet.

2SA1419, 2SC3649

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$)

Symbol	Parameter	Conditions	Ratings			Unit
			Min	Typ	Max	
I_{CBO}	Collector Cutoff Current	$V_{CB} = (-)120\text{ V}, I_E = 0\text{ A}$	-	-	(-) 1	μA
I_{EBO}	Emitter Cutoff Current	$V_{EB} = (-)4\text{ V}, I_C = 0\text{ A}$	-	-	(-) 1	μA
h_{FE1}	DC Current Gain	$V_{CE} = (-)5\text{ V}, I_C = (-)100\text{ mA}$	100*	-	400*	
h_{FE2}		$V_{CE} = (-)5\text{ V}, I_C = (-)10\text{ mA}$	80	-	-	
f_T	Gain-Bandwidth Product	$V_{CE} = (-)10\text{ V}, I_C = (-)50\text{ mA}$	-	120	-	MHz
C_{ob}	Output Capacitance	$V_{CB} = (-)10\text{ V}, f = 1\text{ MHz}$	-	(22)14	-	pF
$V_{CE(sat)}$	Collector-to-Emitter Saturation Voltage	$I_C = (-)500\text{ mA}, I_B = (-)50\text{ mA}$	-	(-200) 130	(-500) 450	mV
$V_{BE(sat)}$	Base-to-Emitter Saturation Voltage	$I_C = (-)500\text{ mA}, I_B = (-)50\text{ mA}$	-	(-) 0.85	(-) 1.2	V
$V_{(BR)CBO}$	Collector-to-Base Breakdown Voltage	$I_C = (-)10\text{ }\mu\text{A}, I_E = 0\text{ A}$	(-) 180	-	-	V
$V_{(BR)CEO}$	Collector-to-Emitter Breakdown Voltage	$I_C = (-)1\text{ mA}, R_{BE} = \infty$	(-) 160	-	-	V
$V_{(BR)EBO}$	Emitter-to-Base Breakdown Voltage	$I_E = (-)10\text{ }\mu\text{A}, I_C = 0\text{ A}$	(-) 6	-	-	V
t_{on}	Turn-ON Time	See specified Test Circuit	-	(40) 40	-	ns
t_{stg}	Storage Time		-	(0.7) 1.2	-	μs
t_f	Fall Time		-	(40) 80	-	ns

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

* The 2SA1419 / 2SC3649 are classified by 100 mA h_{FE} as follows:

Rank	R	S	T
h_{FE}	100 to 200	140 to 280	200 to 400




Figure 1. Switching Time Test Circuit

TYPICAL CHARACTERISTICS




Figure 2. $I_C - V_{CE}$




Figure 3. $I_C - V_{CE}$




Figure 4. $I_C - V_{CE}$




Figure 5. $I_C - V_{CE}$




Figure 6. $I_C - V_{BE}$




Figure 7. $I_C - V_{BE}$

2SA1419, 2SC3649

TYPICAL CHARACTERISTICS (continued)




Figure 8. $h_{FE} - I_C$




Figure 9. $h_{FE} - I_C$




Figure 10. $f_T - I_C$




Figure 11. $C_{ob} - V_{CB}$




Figure 12. $V_{CE(sat)} - I_C$




Figure 13. $V_{CE(sat)} - I_C$

2SA1419, 2SC3649

TYPICAL CHARACTERISTICS (continued)




Figure 14. $V_{BE(sat)} - I_C$




Figure 15. $V_{BE(sat)} - I_C$




Figure 16. ASO




Figure 17. $P_C - T_A$


ORDERING INFORMATION

Device	Package	Shipping [†]
2SA1419S-TD-E	SOT-89 / PCP-1 (Pb-Free)	1000 / Tape & Reel
2SA1419T-TD-E	SOT-89 / PCP-1 (Pb-Free)	1000 / Tape & Reel
2SA1419T-TD-H	SOT-89 / PCP-1 (Pb-Free, Halide Free)	1000 / Tape & Reel
2SC3649S-TD-E	SOT-89 / PCP-1 (Pb-Free)	1000 / Tape & Reel
2SC3649S-TD-H	SOT-89 / PCP-1 (Pb-Free & Halogen Free)	1000 / Tape & Reel
2SC3649T-TD-E	SOT-89 / PCP-1 (Pb-Free)	1000 / Tape & Reel
2SC3649T-TD-H	SOT-89 / PCP-1 (Pb-Free & Halogen Free)	1000 / Tape & Reel

[†]For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, [BRD8011/D](#).

SOT-89 / PCP-1
CASE 419AU
ISSUE 0

DATE 30 APR 2012



DOCUMENT NUMBER:	98AON79746E	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	SOT-89 / PCP-1	PAGE 1 OF 1

onsemi and Onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

onsemi, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at www.onsemi.com/support/sales



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[onsemi:](#)

[2SC3649S-TD-H](#) [2SC3649T-TD-H](#) [2SA1419T-TD-H](#) [2SA1419S-TD-H](#) [2SA1419S-TD-E](#) [2SA1419T-TD-E](#)
[2SC3649S-TD-E](#) [2SC3649T-TD-E](#)