

Bipolar Transistor

(–)50 V, (–)2 A, Low VCE(sat),
(PNP)NPN Single TP/TP-FA

2SB1201/2SD1801

Features

- Adoption of FBET, MBIT Processes
- Low Collector-to-Emitter Saturation Voltage
- Small and Slim Package Making it Easy to Make 2SB1201 / 2SD1801 – Used Sets Smaller
- Large Current Capacitance and Wide ASO
- These are Pb-Free Devices

Applications



- Voltage Regulators, Relay Drivers, Lamp Drivers, Electrical Equipment

ABSOLUTE MAXIMUM RATINGS (at Ta = 25°C)



Parameter	Symbol	Conditions	Ratings	Unit
Collector-to-Base Voltage	V _{CBO}		(–)60	V
Collector-to-Emitter Voltage	V _{CEO}		(–)50	V
Emitter-to-Base Voltage	V _{EBO}		(–)6	V
Collector Current	I _C		(–)2	A
Collector Current (Pulse)	I _{CP}		(–)4	A
Collector Dissipation	P _C		0.8	W
		T _C = 25°C	15	W
Junction Temperature	T _J		150	°C
Storage Temperature	T _{stg}		–55 to +150	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.



NOTE: Specifications (): 2SB1201



MARKING DIAGRAMS



ELECTRICAL CONNECTION



ORDERING INFORMATION

Device	Package	Shipping†
2SB1201S-E	IPAK / TP (Pb-Free)	500 pcs / Bag
2SB1201S-TL-E	DPAK / TP-FA (Pb-Free)	700 / Tape & Reel
2SB1201T-TL-E	DPAK / TP-FA (Pb-Free)	700 / Tape & Reel
2SD1801S-TL-E	DPAK / TP-FA (Pb-Free)	700 / Tape & Reel
2SD1801S-E	IPAK / TP (Pb-Free)	500 pcs / Bag

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

2SB1201/2SD1801

ELECTRICAL CHARACTERISTICS (at Ta = 25°C)

Parameter	Symbol	Conditions	Ratings			Unit
			Min	Typ	Max	
Collector Cutoff Current	I_{CBO}	$V_{CB} = (-)50\text{ V}, I_E = 0\text{ A}$	–	–	(–)100	nA
Emitter Cutoff Current	I_{EBO}	$V_{EB} = (-)4\text{ V}, I_C = 0\text{ A}$	–	–	(–)100	nA
DC Current Gain	h_{FE1}	$V_{CE} = (-)2\text{ V}, I_C = (-)100\text{ mA}$	100*	–	560*	–
	h_{FE2}	$V_{CE} = (-)2\text{ V}, I_C = (-)1.5\text{ A}$	40	–	–	–
Gain–Bandwidth Product	f_T	$V_{CE} = (-)10\text{ V}, I_C = (-)50\text{ mA}$	–	150	–	MHz
Output Capacitance	C_{ob}	$V_{CB} = (-)10\text{ V}, f = 1\text{ MHz}$	–	(22)12	–	pF
Collector–to–Emitter Saturation Voltage	$V_{CE(sat)}$	$I_C = (-)1\text{ A}, I_B = (-)50\text{ mA}$	–	(–0.3)0.15	(–0.7)0.4	V
Base–to–Emitter Saturation Voltage	$V_{BE(sat)}$	$I_C = (-)1\text{ A}, I_E = (-)50\text{ mA}$	–	(–)0.9	(–)1.2	V
Collector–to–Base Breakdown Voltage	$V_{(BR)CBO}$	$I_C = (-)10\text{ }\mu\text{A}, I_E = 0\text{ A}$	(–)60	–	–	V
Collector–to–Emitter Breakdown Voltage	$V_{(BR)CEO}$	$I_C = (-)1\text{ mA}, R_{BE} = \infty$	(–)50	–	–	V
Emitter–to–Base Breakdown Voltage	$V_{(BR)EBO}$	$I_E = (-)10\text{ }\mu\text{A}, I_C = 0\text{ A}$	(–)6	–	–	V
Turn–ON Time	t_{on}	See specified Test Circuit.	–	(60)60	–	ns
Storage Time	t_{stg}		–	(450)550	–	ns
Fall Time	t_f		–	30	–	ns

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

NOTE: Specifications (): 2SB1201

*The 2SB1201 / 2SD1801 are classified by 100 mA h_{FE} as follows :

Table 1.

Rank	R	S	T	U
h_{FE}	100 to 200	140 to 280	200 to 400	280 to 560

Switching Time Test Circuit




Figure 1. Switching Time Test Circuit




Figure 2. $I_C - V_{CE}$




Figure 3. $I_C - V_{CE}$




Figure 4. $I_C - V_{CE}$




Figure 5. $I_C - V_{CE}$




Figure 6. $I_C - V_{BE}$




Figure 7. $I_C - V_{BE}$

2SB1201/2SD1801




Figure 8. $h_{FE} - I_C$




Figure 9. $h_{FE} - I_C$




Figure 10. $f_T - I_C$




Figure 11. $f_T - I_C$




Figure 12. $C_{ob} - V_{CB}$




Figure 13. $C_{ob} - V_{CB}$

2SB1201/2SD1801




Figure 14. $V_{CE(sat)} - I_C$




Figure 15. $V_{CE(sat)} - I_C$




Figure 16. $V_{BE(sat)} - I_C$




Figure 17. $V_{BE(sat)} - I_C$




Figure 18. ASO





Figure 19. $P_C - T_a$

DPAK / TP-FA
CASE 369AH
ISSUE O

DATE 30 JAN 2012



Pin 2 is idle pin with electrical
designation only carried.


1:
2:
3:
*1: Lot indication 4:

DOCUMENT NUMBER:	98AON66236E	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	DPAK / TP-FA	PAGE 1 OF 1

onsemi and Onsemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

IPAK / TP
CASE 369AJ
ISSUE O

DATE 30 JAN 2012



DOCUMENT NUMBER:	98AON66237E	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
DESCRIPTION:	IPAK / TP	PAGE 1 OF 1

onsemi and **onsemi** are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.

onsemi, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation
onsemi Website: www.onsemi.com

ONLINE SUPPORT: www.onsemi.com/support

For additional information, please contact your local Sales Representative at
www.onsemi.com/support/sales

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[onsemi:](#)

[2SD1801T-E](#) [2SB1201S-E](#) [2SB1201T-TL-E](#) [2SD1801S-E](#) [2SB1201S-TL-E](#) [2SD1801S-TL-E](#) [2SD1801T-TL-E](#)