

# MOSFET – P-Channel, POWER TRENCH®

**-150 V, -2 A, 307 mΩ**

## FDMC86262P

### General Description

This P-Channel MOSFET is produced using onsemi's advanced POWER TRENCH technology. This very high density process is especially tailored to minimize on-state resistance and optimized for superior switching performance.


### Features

- Max  $r_{DS(on)}$  = 307 mΩ at  $V_{GS} = -10$  V,  $I_D = -2$  A
- Max  $r_{DS(on)}$  = 356 mΩ at  $V_{GS} = -6$  V,  $I_D = -1.8$  A
- Very Low  $r_{DS(on)}$  Mid Voltage P-Channel Silicon Technology Optimised for Low  $Q_g$
- Optimised for Fast Switching Applications as Well as Load Switch Applications
- 100% UIL Tested
- This Device is Pb-Free, Halide Free and is ROHS Compliant

### Applications


- Active Clamp Switch
- Load Switch

$V_{DS}$	$r_{DS(on)}$ MAX	$I_D$ MAX
-150 V	307 mΩ @ -10 V	-2 A
	356 mΩ @ -6 V	




WDFN8 3.3x3.3, 0.65P  
(MLP 3.3x3.3)  
CASE 511DH

### MARKING DIAGRAM



FDMC86262P = Device Code  
&Z = Assembly Plant Code  
&K = 2-Digits Lot Run Traceability Code  
&2 = 2-Digit Date Code Format

### PIN ASSIGNMENT



### ORDERING INFORMATION

See detailed ordering and shipping information on page 6 of this data sheet.

## MOSFET MAXIMUM RATINGS ( $T_C = 25^\circ\text{C}$ unless otherwise noted)

Symbol	Parameter			Ratings	Unit
V <sub>DS</sub>	Drain to Source Voltage			−150	V
V <sub>GS</sub>	Gate to Source Voltage			±25	V
I <sub>D</sub>	Drain Current	Continuous (Note 3)	T <sub>C</sub> = 25°C	−8.4	A
		Continuous (Note 3)	T <sub>C</sub> = 100°C	−5.3	A
		Continuous (Note 4a)	T <sub>A</sub> = 25°C	−2	A
		Pulsed (Note 2)		−35	
E <sub>AS</sub>	Single Pulse Avalanche Energy (Note 1)			37	mJ
P <sub>D</sub>	Power Dissipation		T <sub>C</sub> = 25°C	40	W
	Power Dissipation (Note 4a)		T <sub>A</sub> = 25°C	2.3	
T <sub>J</sub> , T <sub>STG</sub>	Operating and Storage Junction Temperature Range			−55 to +150	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Starting  $T_J = 25^\circ\text{C}$ ,  $L = 3\text{ mH}$ ,  $I_{AS} = -5\text{ A}$ ,  $V_{DD} = -150\text{ V}$ ,  $V_{GS} = -10\text{ V}$ .


2. Pulsed  $I_D$  please refer to Figure 11 SOA graph for more details.

3. Computed continuous current limited to Max Junction Temperature only, actual continuous current will be limited by thermal & electro-mechanical application board design.


## THERMAL CHARACTERISTICS

Symbol	Parameter	Ratings	Unit
$R_{\theta JC}$	Thermal Resistance, Junction-to-Case	3.1	$^\circ\text{C/W}$
$R_{\theta JA}$	Thermal Resistance, Junction-to-Ambient (Note 4a)	53	

4.  $R_{\theta JA}$  is determined with the device mounted on a 1 in<sup>2</sup> pad 2 oz copper pad on a 1.5 x 1.5 in. board of FR-4 material.  $R_{\theta JC}$  is guaranteed by design while  $R_{\theta CA}$  is determined by the user's board design.



a. 53°C/W when mounted on a 1 in<sup>2</sup> pad of 2 oz copper



b. 125°C/W when mounted on a minimum pad of 2 oz copper

# FDMC86262P

## ELECTRICAL CHARACTERISTICS (T<sub>J</sub> = 25°C unless otherwise noted)

Symbol	Parameter	Test Conditions	Min	Typ	Max	Unit
--------	-----------	-----------------	-----	-----	-----	------

### OFF CHARACTERISTICS

BV <sub>DSS</sub>	Drain to Source Breakdown Voltage	I <sub>D</sub> = -250 μA, V <sub>GS</sub> = 0 V	-150	-	-	V
$\frac{\Delta BV_{DSS}}{\Delta T_J}$	Breakdown Voltage Temperature Coefficient	I <sub>D</sub> = -250 μA, referenced to 25°C	-	-86	-	mV/°C
I <sub>DSS</sub>	Zero Gate Voltage Drain Current	V <sub>DS</sub> = -120 V, V <sub>GS</sub> = 0 V	-	-	-1	μA
I <sub>GSS</sub>	Gate to Source Leakage Current	V <sub>GS</sub> = ±25 V, V <sub>DS</sub> = 0 V	-	-	±100	nA

### ON CHARACTERISTICS

V <sub>GS(th)</sub>	Gate to Source Threshold Voltage	V <sub>GS</sub> = V <sub>DS</sub> , I <sub>D</sub> = 250 μA	-2	-2.9	-4	V
$\frac{\Delta V_{GS(th)}}{\Delta T_J}$	Gate to Source Threshold Voltage Temperature Coefficient	I <sub>D</sub> = -250 μA, referenced to 25°C	-	5	-	mV/°C
r <sub>DS(on)</sub>	Static Drain to Source On Resistance	V <sub>GS</sub> = -10 V, I <sub>D</sub> = -2 A	-	241	307	mΩ
		V <sub>GS</sub> = -6 V, I <sub>D</sub> = -1.8 A	-	266	356	
		V <sub>GS</sub> = -10 V, I <sub>D</sub> = -2 A, T <sub>J</sub> = 125°C	-	425	541	
g <sub>FS</sub>	Forward Transconductance	V <sub>DS</sub> = -10 V, I <sub>D</sub> = -2 A	-	5.4	-	S

### DYNAMIC CHARACTERISTICS

C <sub>iss</sub>	Input Capacitance	V <sub>DS</sub> = -75 V, V <sub>GS</sub> = 0 V, f = 1 MHz	-	632	885	pF
C <sub>oss</sub>	Output Capacitance		-	45	65	pF
C <sub>rss</sub>	Reverse Transfer Capacitance		-	1.3	2.0	pF
R <sub>g</sub>	Gate Resistance		0.1	3	6	Ω

### SWITCHING CHARACTERISTICS

t <sub>d(on)</sub>	Turn-On Delay Time	V <sub>DD</sub> = -75 V, I <sub>D</sub> = -2 A, V <sub>GS</sub> = -10 V, R <sub>GEN</sub> = 6 Ω	-	8.5	17	ns
t <sub>r</sub>	Rise Time		-	2.2	10	ns
t <sub>d(off)</sub>	Turn-Off Delay Time		-	15	26	ns
t <sub>f</sub>	Fall Time		-	5.6	11	ns
Q <sub>g</sub>	Total Gate Charge	V <sub>GS</sub> = 0 V to -10 V, V <sub>DD</sub> = -75 V, I <sub>D</sub> = -2 A	-	9.1	13	nC
Q <sub>g</sub>	Total Gate Charge	V <sub>GS</sub> = 0 V to -6 V, V <sub>DD</sub> = -75 V, I <sub>D</sub> = -2 A	-	5.6	7.9	nC
Q <sub>gs</sub>	Gate to Source Charge	V <sub>DD</sub> = -75 V, I <sub>D</sub> = -2 A	-	2.5	-	nC
Q <sub>gd</sub>	Gate to Drain "Miller" Charge		-	1.6	-	nC

### DRAIN-SOURCE DIODE CHARACTERISTICS

V <sub>SD</sub>	Source-Drain Diode Forward Voltage	V <sub>GS</sub> = 0 V, I <sub>S</sub> = -2 A (Note 5)	-	-0.8	-1.3	V
t <sub>rr</sub>	Reverse Recovery Time	I <sub>F</sub> = -2 A, di/dt = 100 A/μs	-	72	116	ns
Q <sub>rr</sub>	Reverse Recovery Charge		-	166	266	nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

5. Pulse Test: Pulse Width < 300 μs, Duty cycle < 2.0%.


TYPICAL CHARACTERISTICS ( $T_J = 25^\circ\text{C}$  UNLESS OTHERWISE NOTED)

Figure 1. On Region Characteristics




Figure 2. Normalized On-Resistance vs. Drain Current and Gate Voltage




Figure 3. Normalized On-Resistance vs. Junction Temperature




Figure 4. On Resistance vs. Gate to Source Voltage




Figure 5. Transfer Characteristics




Figure 6. Source to Drain Diode Forward Voltage vs. Source Current

TYPICAL CHARACTERISTICS ( $T_J = 25^\circ\text{C}$  UNLESS OTHERWISE NOTED) (CONTINUED)




Figure 7. Gate Charge Characteristics




Figure 8. Capacitance vs. Drain to Source Voltage




Figure 9. Unclamped Inductive Switching Capability




Figure 10. Maximum Continuous Drain Current vs. Case Temperature




Figure 11. Forward Bias Safe Operating Area




Figure 12. Single Pulse Maximum Power Dissipation

TYPICAL CHARACTERISTICS ( $T_J = 25^\circ\text{C}$  UNLESS OTHERWISE NOTED) (CONTINUED)




Figure 13. Junction-to-Ambient Transient Thermal Response Curve





PACKAGE MARKING AND ORDERING INFORMATION

Device	Device Marking	Package Type	Reel Size	Tape Width	Shipping <sup>†</sup>
FDMC86262P	FDMC86262P	WDFN8 3.3x3.3, 0.65P Power 33 (Pb-Free, Halide Free)	13"	12 mm	3000 / Tape & Reel

<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

WDFN8 3.3x3.3, 0.65P  
CASE 511DH  
ISSUE O

DATE 31 JUL 2016



## RECOMMENDED LAND PATTERN

NOTES:

- A. DOES NOT CONFORM TO JEDEC REGISTRATION MO-229
- B. DIMENSIONS ARE IN MILLIMETERS.
- C. DIMENSIONS AND TOLERANCES PER ASME Y14.5M, 2009.
- D. LAND PATTERN RECOMMENDATION IS EXISTING INDUSTRY LAND PATTERN.

<b>DOCUMENT NUMBER:</b>	<b>98AON13625G</b>	Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.
<b>DESCRIPTION:</b>	<b>WDFN8 3.3X3.3, 0.65P</b>	<b>PAGE 1 OF 1</b>

**onsemi** and **onsemi** are trademarks of Semiconductor Components Industries, LLC dba **onsemi** or its subsidiaries in the United States and/or other countries. **onsemi** reserves the right to make changes without further notice to any products herein. **onsemi** makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. **onsemi** does not convey any license under its patent rights nor the rights of others.

**onsemi**, **Onsemi**, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "**onsemi**" or its affiliates and/or subsidiaries in the United States and/or other countries. **onsemi** owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of **onsemi**'s product/patent coverage may be accessed at [www.onsemi.com/site/pdf/Patent-Marking.pdf](http://www.onsemi.com/site/pdf/Patent-Marking.pdf). **onsemi** reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and **onsemi** makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

## ADDITIONAL INFORMATION

### TECHNICAL PUBLICATIONS:

Technical Library: [www.onsemi.com/design/resources/technical-documentation](http://www.onsemi.com/design/resources/technical-documentation)  
onsemi Website: [www.onsemi.com](http://www.onsemi.com)

### ONLINE SUPPORT: [www.onsemi.com/support](http://www.onsemi.com/support)

For additional information, please contact your local Sales Representative at  
[www.onsemi.com/support/sales](http://www.onsemi.com/support/sales)



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[onsemi:](#)

[FDMC86262P](#)