NPN Silicon Power Darlington Transistors

MJE5740, MJE5742

The MJE5740 and MJE5742 Darlington transistors are designed for high–voltage power switching in inductive circuits.

Features

• These Devices are Pb-Free and are RoHS Compliant*

Applications

- Small Engine Ignition
- Switching Regulators
- Inverters
- Solenoid and Relay Drivers
- Motor Controls

MAXIMUM RATINGS

Symbol	Rating	Value	Unit
V _{CEO(sus)}	Collector-Emitter Voltage MJE5740 MJE5742	300 400	Vdc
V _{CEV}	Collector-Emitter Voltage MJE5740 MJE5742	600 800	Vdc
V _{EB}	Emitter-Base Voltage	8	Vdc
I _С I _{СМ}	Collector Current – Continuous – Peak (Note 1)	8 16	Adc
I _B I _{BM}	Base Current – Continuous – Peak (Note 1)	2.5 5	Adc
PD	Total Device Dissipation @ $T_A = 25^{\circ}C$ Derate above 25°C	2 0.016	W W/°C
PD	Total Device Dissipation @ $T_C = 25^{\circ}C$ Derate above 25°C	100 0.8	W W/°C
T _J , T _{stg}	Operating and Storage Junction Temperature Range	-65 to +150	°C

THERMAL CHARACTERISTICS

Symbol	Characteristics	Max	Unit
$R_{\theta JC}$	Thermal Resistance, Junction-to-Case	1.25	°C/W
$R_{\theta JA}$	Thermal Resistance, Junction-to-Ambient	62.5	°C/W
ΤL	Maximum Lead Temperature for Soldering Purposes 1/8" from Case for 5 Seconds	275	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

1. Pulse Test: Pulse Width = 5 ms, Duty Cycle \leq 10%.

*For additional information on our Pb-Free strategy and soldering details, please download the **onsemi** Soldering and Mounting Techniques Reference Manual, <u>SOLDERRM/D</u>.

POWER DARLINGTON TRANSISTORS 8 AMPERES 300–400 VOLTS 80 WATTS







MARKING DIAGRAM



ORDERING INFORMATION

See detailed ordering and shipping information in the package dimensions section on page 6 of this data sheet.

NOTE: Some of the devices on this data sheet have been **DISCONTINUED**. Please refer to the table on page 6.

ELECTRICAL CHARACTERISTICS (T_C = 25°C unless otherwise noted)

Symbol	Characteristic	Min	Тур	Max	Unit				
OFF CHARAC	CTERISTICS (Note 2)			_					
V _{CEO(sus)}	Collector-Emitter Sustaining Voltage $(I_{C} = 50 \text{ mA}, I_{B} = 0)$	MJE5740 MJE5742	300 400	-	-	Vdc			
I _{CEV}	$ Collector Cutoff Current (V_{CEV} = Rated Value, V_{BE(off)} = 1.5 Vdc) \\ (V_{CEV} = Rated Value, V_{BE(off)} = 1.5 Vdc, T_C = 100^{\circ}C) $		-	-	1 5	mAdc			
I _{EBO}	Emitter Cutoff Current (V_{EB} = 8 Vdc, I_C = 0)		-	-	75	mAdc			

SECOND BREAKDOWN

I _{S/b}	Second Breakdown Collector Current with Base Forward Biased	See Figure 6
RBSOA	Clamped Inductive SOA with Base Reverse Biased	See Figure 7

ON CHARACTERISTICS (Note 2)

h _{FE}	DC Current Gain (I _C = 0.5 Adc, V _{CE} = 5 Vdc) (I _C = 4 Adc, V _{CE} = 5 Vdc)	50 200	100 400		-
V _{CE(sat)}	$ \begin{array}{l} \mbox{Collector-Emitter Saturation Voltage (I_C = 4 \mbox{ Adc, I}_B = 0.2 \mbox{ Adc}) \\ (I_C = 8 \mbox{ Adc, I}_B = 0.4 \mbox{ Adc}) \\ (I_C = 4 \mbox{ Adc, I}_B = 0.2 \mbox{ Adc, T}_C = 100^{\circ}\mbox{C}) \end{array} $			2 3 2.2	Vdc
V _{BE(sat)}	$\begin{array}{l} \text{Base-Emitter Saturation Voltage (I_C = 4 Adc, I_B = 0.2 Adc)} \\ (I_C = 8 \text{ Adc, } I_B = 0.4 \text{ Adc})} \\ (I_C = 4 \text{ Adc, } I_B = 0.2 \text{ Adc, } T_C = 100^{\circ}\text{C}) \end{array}$			2.5 3.5 2.4	Vdc
V _f	Diode Forward Voltage (Note 3) (I _F = 5 Adc)	-	-	2.5	Vdc

SWITCHING CHARACTERISTICS

Typical Resistive Load (Table 1)									
t _d	Delay Time		-	0.04	-	μs			
t _r	Rise Time	$(V_{CC} = 250 \text{ Vdc}, I_{C(pk)} = 6 \text{ A})$	-	0.5	-	μs			
t _s	Storage Time	$B_1 = B_2 = 0.25 \text{ A}, t_p = 25 \mu\text{s},$ Duty Cycle $\leq 1\%$)	-	8	-	μs			
t _f	Fall Time		-	2	-	μs			
Inductive Lo	Inductive Load, Clamped (Table 1)								
t _{sv}	Voltage Storage Time	(I _{C(pk)} = 6 A, V _{CE(pk)} = 250 Vdc	_	4	-	μs			
t _c	Crossover Time	$I_{B1} = 0.06 \text{ A}, V_{BE(off)} = 5 \text{ Vdc})$	-	2	-	μs			

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions. 2. Pulse Test: Pulse Width 300 μ s, Duty Cycle = 2%.

3. The internal Collector-to-Emitter diode can eliminate the need for an external diode to clamp inductive loads. Tests have shown that the Forward Recovery Voltage (Vf) of this diode is comparable to that of typical fast recovery rectifiers.

TYPICAL CHARACTERISTICS







Table 1. Test Conditions for Dynamic Performance

SAFE OPERATING AREA INFORMATION

FORWARD BIAS

There are two limitations on the power handling ability of a transistor: average junction temperature and second breakdown. Safe operating area curves indicate $I_C - V_{CE}$ limits of the transistor that must be observed for reliable operation; i.e., the transistor must not be subjected to greater dissipation than the curves indicate.

The data of Figure 6 is based on $T_C = 25^{\circ}C$; $T_{J(pk)}$ is variable depending on power level. Second breakdown pulse limits are valid for duty cycles to 10% but must be derated when $T_C \ge 25^{\circ}C$. Second breakdown limitations do not derate the same as thermal limitations. Allowable current at the voltages shown on Figure 6 may be found at any case temperature by using the appropriate curve on Figure 1.

REVERSE BIAS

For inductive loads, high voltage and high current must be sustained simultaneously during turn-off, in most cases, with the base to emitter junction reverse biased. Under these conditions the collector voltage must be held to a safe level at or below a specific value of collector current. This can be accomplished by several means such as active clamping, RC snubbing, load line shaping, etc. The safe level for these devices is specified as Reverse Bias Safe Operating Area and represents the voltage-current condition allowable during reverse biased turnoff. This rating is verified under clamped conditions so that the device is never subjected to an avalanche mode. Figure 7 gives the complete RBSOA characteristics.



The Safe Operating Area figures shown in Figures 6 and 7 are specified ratings for these devices under the test conditions shown.

Figure 6. Forward Bias Safe Operating Area

Figure 7. Reverse Bias Safe Operating Area



RESISTIVE SWITCHING PERFORMANCE

ORDERING INFORMATION

Device	Package	Shipping
MJE5742G	TO–220 (Pb–Free)	50 Units / Rail

DISCONTINUED (Note 4)

MJE5740G TO-220 (Pb-Free)	50 Units / Rail
------------------------------	-----------------

4. **DISCONTINUED:** This device is not recommended for new design. Please contact your **onsemi** representative for information. The most current information on this device may be available on <u>www.onsemi.com</u>.

onsemi

\bigwedge				т	D-220						
				CAS	SE 221A						
				ISS	SUE AK					DATE	13 JAN 2022
SCALE 1:1	4		с — Т U		T SEATING PLANE	NOTES: 1. DIME 2. CONT 3. DIME LEA 4. MAX V	NSIONING TROLLING D NSION Z DE D IRREGUL WIDTH FOR INC MIN.	AND TOLERA IMENSION: II FINES A ZON ARITIES ARE / F102 DEVICI HES MAX.	NCING PER A NCHES E WHERE AL ALLOWED. E = 1.35MM MILLIMI MIN.	ANSI Y14.5N L BODY ANI ETERS MAX.	1, 2009. D
і — т	1	2 3				А	0.570	0.620	14.48	15.75	
<u> </u>	╺┕╶╫╴᠇	┟╌┟┟╌┛───╄				В	0.380	0.415	9.66	10.53	
н т		₩₩				С	0.160	0.190	4.07	4.83	
)(i)	ÍÌ		f I		D	0.025	0.038	0.64	0.96	
Z_		κ '				F	0.142	0.161	3.60	4.09	
		Î				G	0.095	0.105	2.42	2.66	
						H	0.110	0.161	2.80	4.10	
SEE NOTE #4	<u></u> → ╙ ┥	╨ ╫────		Ī I			0.014	0.024	12.70	14.27	
Ň	/		R —				0.045	0.302	1 15	14.27	
	G	-	J -				0.045	0.000	1.15	5.32	
	- I						0.100	0.210	2.54	3.04	
		N -				R	0.080	0.110	2.04	2 79	
						s	0.045	0.055	1.15	1.41	
						Т	0.235	0.255	5.97	6.47	
						U	0.000	0.050	0.00	1.27	
						v	0.045		1.15		
						Z		0.080		2.04	
	STYLE 1: PIN 1. 2. 3. 4. STYLE 5:	BASE COLLECTOR EMITTER COLLECTOR	STYLE 2: PIN 1. 2. 3. 4. STYLE 6:	BASE EMITTER COLLECTOR EMITTER	STYLE 3: PIN 1. 2. 3. 4. STYLE 7:	CATHOD ANODE GATE ANODE	E	STYLE 4: PIN 1. MA 2. MA 3. GA 4. MA STYLE 8:	NIN TERMINAL NIN TERMINAL NITE NIN TERMINAL	1 2 2	
	PIN 1. 2. 3. 4.	GATE DRAIN SOURCE DRAIN	PIN 1. 2. 3. 4.	ANODE CATHODE ANODE CATHODE	PIN 1. 2. 3. 4.	CATHOD ANODE CATHOD ANODE	E	PIN 1. CA 2. AN 3. EX 4. AN	ithode Iode Ternal Trip Iode	/DELAY	
	STYLE 9: PIN 1. 2. 3. 4.	GATE COLLECTOR EMITTER COLLECTOR	STYLE 10 PIN 1. 2. 3. 4.	GATE SOURCE DRAIN SOURCE	STYLE 11: PIN 1. 2. 3. 4.	DRAIN SOURCE GATE SOURCE		STYLE 12: PIN 1. M/ 2. M/ 3. G/ 4. NO	AIN TERMINAL AIN TERMINAL ATE DT CONNECTI	- 1 - 2 ED	

 DOCUMENT NUMBER:
 98ASB42148B
 Electronic versions are uncontrolled except when accessed directly from the Document Repository. Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.

 DESCRIPTION:
 TO-220
 PAGE 1 OF 1

 onsemi and OnSemi are trademarks of Semiconductor Components Industries, LLC dba onsemi or its subsidiaries in the United States and/or other countries. onsemi reserves the right to make changes without further notice to any products herein. onsemi makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does onsemi asime any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. onsemi does not convey any license under its patent rights nor the rights of others.

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or indental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification. Buyer shall indemnify and hold onsemi and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs,

ADDITIONAL INFORMATION

TECHNICAL PUBLICATIONS:

Technical Library: www.onsemi.com/design/resources/technical-documentation onsemi Website: www.onsemi.com

ONLINE SUPPORT: <u>www.onsemi.com/support</u> For additional information, please contact your local Sales Representative at <u>www.onsemi.com/support/sales</u>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

onsemi:

MJE5740 MJE5740G MJE5742 MJE5742G