



- NOTES:
- 1. MATERIAL: SEE TABLE
 - 2. cULus LISTED FOR POWER AND GROUNDING APPLICATIONS
 - 3. DUAL RATED FOR USE WITH COPPER OR ALUMINUM STRANDED CODE CONDUCTOR (LIAS250-56-X ONLY)
 - 4. PARTS ARE RoHS COMPLIANT
 - 5. USE OF OXIDE INHIBITING JOINT COMPOUND LIKE PANDUIT CMP-100 RECOMMENDED.
 - 6. DIMENSIONS IN BRACKETS ARE MILLIMETERS



PART NUMBER	MATERIAL	WIRE RANGE	SCREW TYPE	TIGHTENING TORQUE	PACKAGING QUANTITY	 POWER UL486A-486B	 GROUNDING UL467	DIMENSIONS - IN [mm] ±.02 [.5]				
								A	B	C	STUD HOLE D DIA	E
LICC4-22-TL	COPPER	#14 - #4 CU AWG	1/4-28 SLOTTED STAINLESS STEEL	#14-#10 = 20 IN-LB #8 = 25 IN-LB	250	600V RATING 90° C	YES DIRECT BURIAL RATED	1.06 [27.0]	.75 [19.0]	.39 [9.9]	#12 .22 [5.6]	.19 [4.8]
LICC4-22TP-TL	COPPER, TIN PLATED			#6-#4 = 35 IN-LB	250							
LIAS250-56-X	ALUMINUM, TIN PLATED	#6- #250 kcmil CU/AL AWG	1/2-18 W/ 1/4 HEX KEY STEEL, ZINC PLATED	200 IN-LB	10	600V RATING 90° C AL9CU	YES NOT DIRECT BURIAL RATED	2.20 [55.9]	1.70 [43.2]	.80 [20.3]	5/16" .33 [8.4]	.40 [10.2]

PART NUMBER

SEE TABLE

TITLE

LIAC, LICC Lay-In Lug (Reditek Phase 2) Customer Drawing


CUSTOMER DRAWING

ITEM REVISION NAME

03468NBE/00

DATASET FILE NAME

03468NBE-DC/00

THIRD ANGLE
PROJECTION

MATERIAL

SEE TABLE

DRAWING NUMBER

03468NBE - DC

DRAWN BYJHNU

DATE10-20-23

CHKJHNU

SCALENONE

SHEET 1 OF 1

SIZEB

00	10-20-23	JHNU	JHNU	MRWA	DRAWING RELEASED	135288
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[LICC4-22TP-TL](#) [LICC4-22-TL](#) [LIAS250-56-X](#)