

# NetRunner™ Vertical Cable Managers

## SPECIFICATIONS

The vertical cable manager shall be capable of mounting to EIA racks to manage cables on the front and rear of the rack. The manager shall be molded out of plastic and possess cable management fingers and pass-through holes. The fingers shall provide integral bend radius control and be spaced so that the gaps between the fingers align with EIA rack spaces. The pass-through holes shall provide bend radius control and slots that can be used for securing of cable straps. The vertical manager shall have a cover that can be opened to the left or right 110 degrees. The manager shall be able to accept wire retainers that can be snapped on to the cable management fingers.



## TECHNICAL INFORMATION

<i>Attributes:</i>		Part Number	RU	Height in. (mm)	Width in. (mm)	Depth in. (mm)
		<b>WMPV22E</b>	22	41.5 (1054)	4.9 (125)	12.0 (306)
		<b>WMPVF22E</b>	22	41.5 (1054)	4.9 (125)	6.5 (165)
		<b>WMPV45E</b>	45	83.0 (2108)	4.9 (125)	12.0 (306)
		<b>WMPVF45E</b>	45	83.0 (2108)	4.9 (125)	6.5 (165)
		<b>WMPVHC45E</b>	45	83.0 (2108)	6.7 (170)	14.1 (357)
		<b>WMPVHCF45E</b>	45	83.0 (2108)	6.7 (170)	7.6 (192)
<i>Mounting options:</i>		When attached to the side of a standard 19" EIA rack, the pitch of a WMPV vertical manager is 25.3 in. and the pitch of a WMPVHC vertical manager is 27.1 in.  Managers can be center mounted between two adjacent EIA 19" or 23" racks by using the WMPVCBE bracket kit.  Managers can be mounted to R2PS and 7' R4P series of 4-Post racks by using the WMPVSMK hardware kit; two kits are needed for center mounting.  Managers can be side or center mounted to the front or rear of a rack with dimensions of up to 1 5/8 in. (41.1mm) from the outside edge of a rack to the center of the mounting hole by using the WMPVCMB bracket kit; two kits are needed for center mounting; when attached to the side of a 19" rack using a WMPVCMB bracket kit, the pitch of a WMPV vertical manager is 25.8 in. and the pitch of WMPVHC vertical manager is 27.6 in.				
<i>Packaging:</i>		Managers include hinged covers, mounting brackets and #12 – 24 screws				
<i>Temperature ratings:</i>		Max storage temperature 149°F (65°C); Max operating temperature 140°F (60°C)				

## KEY FEATURES AND BENEFITS

<i>Bend radius fingers:</i>	Align with rack spaces to support cables as they transition to the vertical pathway; pass-through holes maintain cable bend radius ensuring network performance and reliability
<i>Large finger opening:</i>	Each accommodates up to 24 Category 6 cables eliminating the need to remove fingers for cable routing speeding installation and maintenance
<i>Dual hinged cover:</i>	Can be opened 110 degrees to the left or right to provide complete access to the cables inside the vertical pathway
<i>Integral cable retainers:</i>	On the end of each finger to help contain cables within each rack unit to simplify installation and maintenance

### NetRunner Vertical Cable Managers

#### Front and rear

<b>22 RU, 4" x 5":</b>	<a href="#">WMPV22E</a>
<b>45 RU, 4" x 5":</b>	<a href="#">WMPV45E</a>
<b>45 RU, 6" x 6":</b>	<a href="#">WMPVHC45E</a>

#### Front only

<b>22 RU, 4" x 5":</b>	<a href="#">WMPVF22E</a>
<b>45 RU, 4" x 5":</b>	<a href="#">WMPVF45E</a>
<b>45 RU, 6" x 6":</b>	<a href="#">WMPVHCF45E</a>

### Replacement Covers

<b>4" wide:</b>	<a href="#">WMPVHRCE</a>
<b>6" wide:</b>	<a href="#">WMPVHCRCE</a>

### Standard EIA Racks

<b>2-post aluminum rack with #12-24 threaded rails:</b>	<a href="#">R2P+^</a>
<b>4-post steel rack with #12-24 threaded rails:</b>	<a href="#">R4P+^</a>
<b>4-post steel rack with cage nut rails:</b>	<a href="#">R4PCN+^</a>

### NetManager High Capacity Horizontal Cable Managers

<b>Front and rear:</b>	<a href="#">NM*</a>
<b>Front only:</b>	<a href="#">NMF*</a>

### Accessories

<b>Center mount bracket kit:</b>	<a href="#">WMPVCBE</a>
<b>Side mount hardware kit:</b>	<a href="#">WMPVSMK</a>
<b>Rack adapter bracket kit:</b>	<a href="#">WMPVCMB</a>
<b>Cable retainers:</b>	<a href="#">WR5E-X</a>
<b>Rack top trough with waterfall:</b>	<a href="#">WMPVWF</a>
<b>End panel:</b>	<a href="#">WMPV45EPB1</a>

+Heights: 79 (6.5 ft.) or 96 (8 ft.)

^Colors other than black: WH (White)

\*RUs: 1 - 4 (increments of 1)

-X indicates bulk packages of 10 pieces to reduce single-use plastic





All Part Numbers Compliant with the U.S. Trade Agreements Act (TAA) for purchases shipped to the United States.

# NetRunner™ Vertical Cable Manager

## APPLICATIONS

NetRunner Vertical Cable Managers provide a cost-effective solution that organize, manage, and protect network cabling in telecommunication rooms and data centers. Cable management fingers simplify cable routing during installation and maintenance. Bend radius control helps protect cables from kinks, snags, and crushing, ensuring system performance and reliability. Multiple sizes and mounting options allow for use in a variety of applications. When used with Mini-Com® Patch Panels, patch cords, horizontal cable managers and racks, the user receives a complete end-to-end solution that satisfies functional requirements and showcases network cabling.



Dimensions are in inches. [Dimensions in brackets are metric].

### WORLDWIDE SUBSIDIARIES AND SALES OFFICES

PANDUIT US/CANADA  
Phone: 800.777.3300

PANDUIT EUROPE LTD.  
London, UK  
Phone: 44.20.8601.7200

PANDUIT SINGAPORE PTE. LTD.  
Republic of Singapore  
Phone: 65.6305.7575

PANDUIT JAPAN  
Tokyo, Japan  
Phone: 81.3.6863.6000

PANDUIT LATIN AMERICA  
Guadalajara, Mexico  
Phone: 52.33.3777.6000

PANDUIT AUSTRALIA PTY. LTD.  
Victoria, Australia  
Phone: 61.3.9794.9020

For a copy of Panduit product warranties, log on to [www.panduit.com/warranty](http://www.panduit.com/warranty)

**PANDUIT®**

For more information  
**Visit us at [www.panduit.com](http://www.panduit.com)**  
Contact Customer Service by email: [cs@panduit.com](mailto:cs@panduit.com)  
or by phone: 800.777.3300

© 2024 Panduit Corp.  
ALL RIGHTS RESERVED.  
RKSP112-WW-ENG  
3/2024

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[WMPV22E](#) [WMPV45E](#) [WMPVHCF45E](#) [WMPVF45E](#) [WMPVHC45E](#) [WMPVF22E](#) [WMPVHRCE](#) [WMPVHCRCE](#)