# **Amplifier Transistors**

## **NPN Silicon**

### **Features**

• These are Pb-Free Devices\*



Rating	Symbol	Value	Unit
Collector – Emitter Voltage	V <sub>CEO</sub>	50	Vdc
Collector - Base Voltage	V <sub>CBO</sub>	60	Vdc
Emitter-Base Voltage	V <sub>EBO</sub>	6.0	Vdc
Collector Current – Continuous	I <sub>C</sub>	100	mAdc
Total Device Dissipation @ T <sub>A</sub> = 25°C Derate above 25°C	P <sub>D</sub>	350 2.8	mW mW/°C
Total Device Dissipation @ T <sub>C</sub> = 25°C Derate above 25°C	P <sub>D</sub>	1.0 8.0	W mW/°C
Operating and Storage Junction Temperature Range	T <sub>J</sub> , T <sub>stg</sub>	-55 to +150	°C

### THERMAL CHARACTERISTICS


Characteristic	Symbol	Max	Unit
Thermal Resistance, Junction-to-Ambient	$R_{\theta JA}$	357	°C/W
Thermal Resistance, Junction-to-Case	$R_{\theta JC}$	125	°C/W


Stresses exceeding Maximum Ratings may damage the device. Maximum Ratings are stress ratings only. Functional operation above the Recommended Operating Conditions is not implied. Extended exposure to stresses above the Recommended Operating Conditions may affect device reliability.




### ON Semiconductor®

### http://onsemi.com





### MARKING DIAGRAM



A = Assembly Location

Y = Year WW = Work Week = Pb-Free Package

(Note: Microdot may be in either location)

### **ORDERING INFORMATION**

Device	Package	Shipping <sup>†</sup>
BC182G	TO-92 (Pb-Free)	5000 Units / Bulk
BC182BG	TO-92 (Pb-Free)	5000 Units / Bulk
BC182BRL1G	TO-92 (Pb-Free)	2000 / Tape & Reel

<sup>†</sup>For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specifications Brochure, BRD8011/D.

<sup>\*</sup>For additional information on our Pb–Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

## **ELECTRICAL CHARACTERISTICS** ( $T_A = 25^{\circ}C$ unless otherwise noted)

Characteristic		Symbol	Min	Тур	Max	Unit
OFF CHARACTERISTICS				•	•	
Collector – Emitter Breakdown Voltage $(I_C = 2.0 \text{ mA}, I_B = 0)$		V <sub>(BR)CEO</sub>	50	_	_	V
Collector – Base Breakdown Voltage ( $I_C = 10 \mu A, I_E = 0$ )		V <sub>(BR)CBO</sub>	60	-	_	V
Emitter – Base Breakdown Voltage ( $I_E = 100 \mu A$ , $I_C = 0$ )		V <sub>(BR)EBO</sub>	6.0	-	_	V
Collector Cutoff Current (V <sub>CB</sub> = 50 V, V <sub>BE</sub> = 0)		I <sub>CBO</sub>	_	0.2	15	nA
Emitter–Base Leakage Current (V <sub>EB</sub> = 4.0 V, I <sub>C</sub> = 0)		I <sub>EBO</sub>	_	-	15	nA
ON CHARACTERISTICS						
DC Current Gain (I <sub>C</sub> = 10 $\mu$ A, V <sub>CE</sub> = 5.0 V)	BC182	h <sub>FE</sub>	40	_	-	_
$(I_C = 2.0 \text{ mA}, V_{CE} = 5.0 \text{ V})$	BC182 BC182B		120 180	_ _	500 500	
$(I_C = 100 \text{ mA}, V_{CE} = 5.0 \text{ V})$	BC182		80	-	-	
Collector – Emitter On Voltage ( $I_C = 10 \text{ mA}$ , $I_B = 0.5 \text{ mA}$ ) ( $I_C = 100 \text{ mA}$ , $I_B = 5.0 \text{ mA}$ ) (Note 1)		V <sub>CE(sat)</sub>	_ _	0.07 0.2	0.25 0.6	V
Base – Emitter Saturation Voltage (I <sub>C</sub> = 100 mA, I <sub>B</sub> = 5.0 mA) (Note 1)		V <sub>BE(sat)</sub>	_	-	1.2	V
Base–Emitter On Voltage ( $I_C = 100 \mu A, V_{CE} = 5.0 V$ ) ( $I_C = 2.0 mA, V_{CE} = 5.0 V$ ) ( $I_C = 100 mA, V_{CE} = 5.0 V$ ) (Note 1)		V <sub>BE(on)</sub>	- 0.55 -	0.5 0.62 0.83	- 0.7 -	V
DYNAMIC CHARACTERISTICS						
Current – Gain — Bandwidth Product ( $I_C = 0.5$ mA, $V_{CE} = 3.0$ V, $f = 100$ MHz) ( $I_C = 10$ mA, $V_{CE} = 5.0$ V, $f = 100$ MHz)		f <sub>T</sub>	_ 150	100 200		MHz
Common Base Output Capacitance (V <sub>CB</sub> = 10 V, I <sub>C</sub> = 0, f = 1.0 MHz)		$C_{\sf ob}$	_	-	5.0	pF
Common Base Input Capacitance (V <sub>EB</sub> = 0.5 V, I <sub>C</sub> = 0, f = 1.0 MHz)		C <sub>ib</sub>	_	8.0	_	pF
Small–Signal Current Gain ( $I_C = 2.0 \text{ mA}, V_{CE} = 5.0 \text{ V}, f = 1.0 \text{ kHz}$ )	BC182 BC182B	h <sub>fe</sub>	125 240	- -	500 500	-
Noise Figure (I <sub>C</sub> = 0.2 mA, V <sub>CE</sub> = 5.0 V, R <sub>S</sub> = 2.0 k $\Omega$ , f = 1.0 kHz)		NF	_	2.0	10	dB

<sup>1.</sup> Pulse Test: Tp 300 s, Duty Cycle 2.0%.




Figure 1. Normalized DC Current Gain




Figure 1. "Saturation" and "On" Voltages




Figure 2. Current-Gain — Bandwidth Product




Figure 3. Capacitances





Figure 4. Base Spreading Resistance

### PACKAGE DIMENSIONS

TO-92 (TO-226) CASE 29-11 **ISSUE AM** 




STRAIGHT LEAD **BULK PACK** 



### NOTES:

- 1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982. CONTROLLING DIMENSION: INCH.
- CONTOUR OF PACKAGE BEYOND DIMENSION R IS UNCONTROLLED
- LEAD DIMENSION IS UNCONTROLLED IN P AND BEYOND DIMENSION K MINIMUM.

	INCHES		MILLIN	IETERS
DIM	MIN	MAX	MIN	MAX
Α	0.175	0.205	4.45	5.20
В	0.170	0.210	4.32	5.33
С	0.125	0.165	3.18	4.19
D	0.016	0.021	0.407	0.533
G	0.045	0.055	1.15	1.39
Н	0.095	0.105	2.42	2.66
J	0.015	0.020	0.39	0.50
K	0.500		12.70	
L	0.250		6.35	
N	0.080	0.105	2.04	2.66
P		0.100		2.54
R	0.115		2.93	
٧	0.135		3.43	



**BENT LEAD** TAPE & REEL AMMO PACK



#### NOTES:

- DIMENSIONING AND TOLERANCING PER ASME Y14.5M, 1994.
- CONTROLLING DIMENSION: MILLIMETERS.
  CONTOUR OF PACKAGE BEYOND
- DIMENSION R IS UNCONTROLLED
- LEAD DIMENSION IS UNCONTROLLED IN PAND BEYOND DIMENSION K MINIMUM.

	MILLIMETERS		
DIM	MIN	MAX	
Α	4.45	5.20	
В	4.32	5.33	
С	3.18	4.19	
D	0.40	0.54	
G	2.40	2.80	
J	0.39	0.50	
K	12.70		
N	2.04	2.66	
P	1.50	4.00	
R	2.93		
V	3.43		

STYLE 17:

COLLECTOR PIN 1.

BASE

EMITTER

ON Semiconductor and un are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice on semiconductor and are registered readerlands of semiconductor Components industries, Ltc (SciLLC). Solitude services the inject to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications. intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

### PUBLICATION ORDERING INFORMATION

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor P.O. Box 5163, Denver, Colorado 80217 USA

Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free USA/Canada

Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910 Japan Customer Focus Center

Phone: 81-3-5773-3850

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

# **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

# **ON Semiconductor:**

BC182 BC182A BC182AG BC182B BC182BG BC182BRL1 BC182BRL1G BC182G