

Device connector, front mounting - HC-26P1N8AWA00 - 1623268

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Device connector, front mounting, straight, Screw locking, M27, number of positions: 26, type of contact: Pin, Crimp connection, Radial O-ring, 4x Ø 3.2, shielded: yes, flange dimensions: 30 mm x 30 mm

RoHS

Key Commercial Data

Packing unit	24 pc
GTIN	
GTIN	4055626272917

Technical data

General

Note	Order information: Order crimp contacts Ø 1 mm separately
Type of locking	Screw locking
Direction of rotation of contact chamber numbering	Standard
Coding	N
Contact connection method	Crimp connection
Type of contacts	Pin
Number of positions	26
Contact diameter of power contacts	1 mm
Nominal current per power contact at 25°C	8 A
Pg housing screw connection	none
Mounting type	4x Ø 3.2

Ambient conditions

Degree of protection	IP67, when plugged in
----------------------	-----------------------

Specifications according to DIN EN 61984:2001

Nominal / operating voltage of power contacts	150 V
Rated surge voltage of power contacts	1.5 kV
Overvoltage category of power contacts	II

Device connector, front mounting - HC-26P1N8AWA00 - 1623268

Technical data

Specifications according to DIN EN 61984:2001


Degree of pollution of power contacts	3
---------------------------------------	---

Environmental Product Compliance


REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"

Drawings

Schematic diagram




Dimensional drawing



Installation dimensions

Dimensional drawing



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1623268](#)