


ALL DIMENSIONS ARE IN (mm)						
Part Number	Wire Size	Wire Class	Wire Strip Length	$l \pm 2.76$	$o \pm .50$	$i \pm .50$
SCMSX10-C	10 mm ²	5f & 6f	19.0	35.0	7.20	5.50
SCMSX16-C	16 mm ²	5f & 6f	26.0	49.0	9.10	6.90
SCMSX25-L	25 mm ²	5f & 6f	19.5	36.0	10.40	8.20
SCMSX35-L	35 mm ²	5f & 6f	30.0	57.0	12.70	9.80
SCMSX50-L	50 mm ²	5f & 6f	27.5	52.0	14.20	11.50
SCMSX70-L	70 mm ²	5f & 6f	28.5	54.0	17.40	13.50
SCMSX95-Q	95 mm ²	5f & 6f	30.0	57.0	19.40	15.20
SCMSX120-Q	120 mm ²	5f & 6f	30.0	57.0	21.00	16.50
SCMSX150-X	150 mm ²	5f & 6f	32.0	61.0	23.00	18.60
SCMSX185-X	185 mm ²	5f & 6f	37.5	72.0	26.00	20.80
SCMSX240-X	240 mm ²	5f & 6f	39.0	75.0	29.00	23.50
SCMSX300-5	300 mm ²	5f	49.0	95.0	33.00	26.20

- NOTES:
1. Material: High conductivity seamless copper tube.
 2. Plating: Parts are annealed and tin plated.
 3. WireType: Class 5 and 6 Flexible Stranded Copper Conductor per DIN VDE 0295, IEC 60228, and HD 383.
 4. UL Listed & CSA Certified Wire Connectors for applications up to 35kv, when crimped per instruction sheet included with Panduit packaging. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.
 5. UL & CSA Temperature Rating: 90°C



LISTED
Wire Connector



CERTIFIED

										PANDUIT CORP. TINLEY PARK, ILLINOIS METRIC FLEX SPLICES - SCMSX SERIES 10-300mm ² CUSTOMER DRAWING				
														UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± (.XX) ± ANGLES ±
00		11/12	TLCO	TLCO	DRAWING RELEASED			10N014BE-NC	RGB	RGB	DRAWN BY TLCO		MAT'L: NONE	
REV	DATE	BY	CHK	DESCRIPTION			ECN	-R	SUP	CHK'D	TLCO	DRAWING NO / CAD FILE 10N014BE-NC		DWG B SIZE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[SCMSX300-5](#)