



## 45 Watt USB Power Delivery 2.0 Adapter with USB-C



### Features

- USB-C
- Class B EMI
- Limited Power Source (LPS)
- OVP, OCP, OTP & Short Circuit Protection
- DOE Level VI, CoC V5 Tier 2

### Applications

- Mobile Phone
- Tablet
- Notebook
- Networking Devices
- Monitor

### Safety Approvals

- U/cUL
- CB
- CE

### Mechanical Characteristics

- Length: 67mm (2.64in)
- Width: 48mm (1.89in)
- Height: 29mm (1.41in)
- Weight: 145g (.32lbs)

### Output Specifications

Model	Prong Style	DC Output Voltage	Current Rating	Ripple <sup>(1)</sup> P-P (max.)
AQ45A-5CKA-H	US	5V/12V/20V	3A/3A/2.25A	200mV
AQ45E-5CKA-H	EU	5V/12V/20V	3A/3A/2.25A	200mV

Notes: (1) Measured by using a 12 inch twisted pair terminated with a 10uF & 0.1uF ceramic in parallel. Oscilloscope is set to 20MHz.

PhiHong is not responsible for any error, and reserves the right to make changes without notice. Please visit our website at [www.phihong.com](http://www.phihong.com) for the most up-to-date specifications and contact information.

**Input:****AC Input Voltage Rating**

100 to 240V AC

**AC Input Voltage Range**

90 to 264V AC

**AC Input Frequency**

50 to 60Hz

**Input Current**

&lt;1A (RMS) maximum at 90Vac @max load

**Leakage Current**

0.25mA Max.

**Inrush Current**

90Amax @240Vac/50Hz (Cold start)

**Input Power Saving**

.075W max @230VAC /50Hz

**Output:****Efficiency**

US DOE Level VI

CoC V5 Tier 2

**Environmental:****Temperature**

Operation 0 to +45°C

Non-operation -40 to +85°C

Humidity 90% RH max

**DC Output Connector**

USB Type C

**Emissions**

Complies with FCC Class B

Complies with EN55032 Class B

**Immunity**

IEC61000-4-2:

Level 2, Contact  $\pm 4\text{KV}$ , Criteria BLevel 3, Air  $\pm 8\text{KV}$ , Criteria BLevel 4, Contact  $\pm 8\text{KV}$ , Criteria CLevel 4, Air  $\pm 15\text{KV}$ , Criteria C

IEC61000-4-3, Level 2, Criteria A

IEC61000-4-4, Level 2, Criteria B

IEC61000-4-5, Level 3, Criteria B

IEC61000-4-6, Level 2, Criteria A

IEC61000-4-8, Level 1, Criteria A

**Hold-up Time**10.3ms minimum at 110V/60Hz, Output  
20V/2.25A**Over-Voltage Protection**


&lt;24Vshutdown

**Over-Temperature Protection**


Shutdown mode

**Over-Current Protection**Output current shall not exceed  
4.5A@5&12V, 4A@20V**Short-Circuit Protection**


Auto Recover

**Dielectric Withstand (Hi-pot) Test**Primary to Secondary: 3000V AC for 1 min.,  
10Ma

**AQ45A-5CKA Dimension Diagram Unit: mm (inch)**



**AQ45E-5CKA Dimension Diagram Unit: mm (inch)**



**Supplier's Declaration of Conformity  
47 CFR § 2.1077 Compliance Information**

**AQ45A-5CKA-H**

Phihong USA Corporation  
47800 Fremont Boulevard  
Fremont, CA 94538  
Telephone: (510) 445-0100  
[www.phihong.com](http://www.phihong.com)

NOTE: This model has/The models in this products series have been tested and found to comply with the limits for a Class B digital device, pursuant to part 15 of the FCC Rules. These limits are designed to provide reasonable protection against harmful interference in a residential installation. This equipment generates, uses and can radiate radio frequency energy and, if not installed and used in accordance with the instructions, may cause harmful interference to radio communications. However, there is no guarantee that interference will not occur in a particular installation. If this equipment does cause harmful interference to radio or television reception, which can be determined by turning the equipment off and on, the user is encouraged to try to correct the interference by one or more of the following measures:

- Reorient or relocate the receiving antenna.
- Increase the separation between the equipment and receiver.
- Connect the equipment into an outlet on a circuit different from that to which the receiver is connected.
- Consult the dealer or an experienced radio/TV technician for help.

Changes or modifications to equipment not expressly approved by PHIHONG could void the user's authority to operate the equipment.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Phihong:

[AQ45A-5CKA](#) [AQ45E-5CKA](#)