

# PYA10A050200



## 10W 5V Fixed Blade Wall Mount Adapter



### Features

- US Wall Plug Fixed Type
- US DoE Level VI Efficiency Compliance
- Load Regulation: +/-5%
- No Load power consumption < 0.075W
- Over-Voltage, Over-Current and Short Circuit Protection
- Color: Black

### Applications

- Smart Home Devices
- Set-top Devices
- Telecommunication
- Electronic Devices
- Office Equipment

### Description

Phihong PYA10A050200 10-watt 5-volt fixed blade wall adapter is a compact and reliable power solution designed to meet the charging needs of various electronic devices. With its fixed blade design, this adapter plugs directly into a standard wall outlet without the need for a detachable power cord. The compact adapter is efficient and minimizes power consumption, meeting Efficiency Level VI requirements as well as Level VII limits proposed by the US Department of Energy in 2023.

Phihong, a reputable manufacturer known for its high-quality power solutions, has certified the adapter to cULus 62368-1 and has integrated safety features such as over-voltage protection, over-current protection, and short-circuit protection into the adapter to help prevent damage to the powered device, providing a peace of mind to users.

# PYA10A050200




## Specifications<sup>1</sup>

Model		PYA10A050200
Output	DC Output Voltage	5V
	Max Current	2.0A
	Output Power	10.0W
	Regulation	± 1% Line / ± 5% Load
	Ripple & Noise P-P(max) <sup>2</sup>	100mV
Input	AC Input Voltage Range	90 to 264VAC
	AC Input Frequency	47 to 63Hz
	AC Input Current	0.4A max. @ input 100-240VAC, full load
	AC Inrush Current	40A max. @ input 240VAC (cold start)
	No Load Power Consumption at 115VAC Input	≤ 0.075W
	115VAC Average Efficiency <sup>3</sup>	≥ 79.0%
	Leakage Current	0.25mA max. at 264VAC/50Hz max., no load
Protection	Over-Voltage	15V max
	Short Circuit	Auto-recovery and no damage.
	Over-Current	4.0A max, auto-recovery
Environmental	Operating Temperature	0°C to +40°C
	Non-Operating Temperature	-20°C to +70°C
	Operating Humidity	10% to 95% RH max
Safety Approvals and EMC	Dielectric Withstand (HI-POT)	Primary to Secondary: 3000VAC, 10mA max. 1 min.
	Insulation Resistance	Primary to Secondary: Min. 50M OHM at 500 VDC
	Standards	cULus 62368-1
	EMI Emissions	FCC Part 15 Class B, CAN ICES-003(B)/NMB-003(B) Conducted & Radiated
	Harmonic Current Emissions	IEC 61000-3-2
	Voltage Fluctuations & Flicker	IEC 61000-3-3
	Immunity	EN 55035/CISPR 35: IEC 61000-4-2 (+/-8kV air, +/- 4kV contact), IEC 61000-4-3, IEC 61000-4-4, IEC 61000-4-5 (2KV L-L, 1KV L-FG), IEC 61000-4-6, IEC 61000-4-8, IEC 61000-4-11
Mechanical	Dimensions (L x W x H)	59.0mm (2.32in) x 40.9mm (1.61in) x 32.4mm (1.27in)
	Cable Length & Gauge	1500mm 22AWG
	DC Output Connector	2.1mm (+) x 5.5mm (-) x 10mm
MTBF	Telcordia (SR-332 Issue 3)	>1,000,000 Hours min. at 264VAC/50Hz, max. load, 25°C
Notes	<ol style="list-style-type: none"> <li>The specifications defined are at ambient temperature of 25C, unless otherwise specified.</li> <li>20MHz bandwidth frequency oscilloscope, add a 0.1μF multilayer Cap. and Low ESR Electrolytic Cap. (10μF) at output connector terminals (nominal line voltage, full load).</li> <li>Efficiency is measured after 30 minutes burn-in.</li> </ol>	

# PYA10A050200

## Outline Drawing





Supplier's Declaration of Conformity  
47 CFR § 2.1077 Compliance Information

MODEL  
PYA10A050200

Phihong USA Corporation  
47800 Fremont Boulevard

Fremont, CA 94538

Telephone: (510) 445-0100

[www.phihong.com](http://www.phihong.com)

*This device complies with part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) This device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.*

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phihong:](#)

[PYA10A050200](#)