

## I/O extension module - NLC-IO-06I-04QTN-01A - 2701085

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




I/O extension module for use with Nanoline base unit. Equipped with 6 digital input and 4 NPN digital output channels. A maximum of three I/O extension modules can be attached to a base unit.

### Your advantages

- Automatically recognized by the firmware
- I/O modules are electrically isolated
- Up to 3 modules can be added to the right side of a base unit
- Can be powered from a secondary power supply

### Key Commercial Data

Packing unit	1 pc
GTIN	 4 046356 325325
GTIN	4046356325325

### Technical data

#### Note

Utilization restriction	EMC: class A product, see manufacturer's declaration in the download area
-------------------------	---

#### Dimensions

Width	40 mm
Height	103.5 mm
Depth	43 mm

#### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 60 °C
Ambient temperature (storage/transport)	-25 °C ... 85 °C

#### Supply

## I/O extension module - NLC-IO-06I-04QTN-01A - 2701085

### Technical data

#### Supply

Connection method	Screw connection
Supply voltage	24 V DC
Supply current	typ. 50 mA
	max. 90 mA

#### Digital inputs

Input name	Digital inputs
Description of the input	PNP/NPN
Connection method	Screw connection
Number of inputs	6
Typical response time	60 µs (on)
	70 µs (OFF)
Input voltage range "0" signal	0 V DC ... 5 V DC
Input voltage range "1" signal	15 V DC ... 30 V DC
Nominal input current at U <sub>IN</sub>	5 mA DC (On)

#### Digital outputs

Output name	Digital outputs
Output description	NPN outputs
Connection method	Screw connection
Number of outputs	4
Type of protection	Short-circuit and overload protection
Maximum output current per channel	500 mA
Maximum output current per module / terminal block	2 A
Maximum output current per module	2 A
Nominal load, inductive	12 VA ((1.2H))
Nominal load, lamp	12 W
Nominal load, ohmic	12 W

#### General

Mounting type	DIN rail mounting
---------------	-------------------


#### Environmental Product Compliance

China RoHS	Environmentally Friendly Use Period = 50
	For details about hazardous substances go to tab "Downloads", Category "Manufacturer's declaration"


#### Drawings

# I/O extension module - NLC-IO-06I-04QTN-01A - 2701085

Dimensional drawing



Connection diagram



## Approvals

### Approvals

Approvals

UL Listed

Ex Approvals

### Approval details

UL Listed		<a href="http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm">http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm</a>	FILE E 238705
-----------	--	---	---------------

Phoenix Contact 2018 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2701085](#)