

# Photovoltaic connector - PV-FT-CF-C-4-300-BU-SP - 1705196


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Photovoltaic connector, Photovoltaic connector, color: black, Min. wire cross section: 4, Connection method: Crimp, Type of contact: Socket, Cable length: 300. can only be released using a tool



## Key Commercial Data

Packing unit	50 pc
Minimum order quantity	50 pc
GTIN	 4 046356 759328
GTIN	4046356759328

## Technical data

### Dimensions

Fixed cable length	300 mm
External cable diameter	4.6 mm ±0.15 mm

### Ambient conditions

Degree of protection (when plugged in)	IP66 / IP68 (2 m / 24 h)
Degree of protection (not plugged in)	IP65
Ambient temperature (operation)	-40 °C ... 85 °C
Ambient temperature (assembly)	-25 °C ... 50 °C

### General

Design	Socket
Tightening torque nut	1.8 Nm ±0.1 Nm
Insertion force	45 N ±10 N
Disconnect force	250 N ±50 N
Pull-out force of cable >= disconnect force	> 80 N
Rated voltage	1500 V
Rated current (4.0 mm²)	40 A
Nominal cross section	4 mm²

# Photovoltaic connector - PV-FT-CF-C-4-300-BU-SP - 1705196

## Technical data

### General

Protection class	II
------------------	----

### Material

Color	black
Insulating material	mPPE
Contact material	Cu
Contact surface material	Ag
Flammability rating according to UL 94	V0

### Connection data

Connection method	Crimp
Connection capacity	4 mm <sup>2</sup>
Contact resistance with connected conductor	0.45 mΩ
Cable type	S02

### Conductor

Outer sheath, material	PE-X
External sheath, color	blue

### Standards and Regulations


Flammability rating according to UL 94	V0
--	----

### Environmental Product Compliance


China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

## Drawings

Dimensional drawing



Dimensional drawing



Dimension x = cable length  
 c: panel thickness - plastic: 2 - 6 mm; metal: 2 - 5 mm

## Approvals

### Approvals

# Photovoltaic connector - PV-FT-CF-C-4-300-BU-SP - 1705196

## Approvals


### Approvals


TÜV Rheinland / VDE Zeichengenehmigung / EAC

### Ex Approvals

### Approval details

TÜV Rheinland	<a href="http://www.certipedia.com">http://www.certipedia.com</a>	R 60126961
Nominal voltage UN	1500 V	

VDE Zeichengenehmigung		<a href="http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx">http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx</a>	40031807
Nominal voltage UN		1500 V	
Nominal current IN		40 A	
mm <sup>2</sup> /AWG/kcmil		4	

EAC		B.01742
-----	---	---------

Phoenix Contact 2018 © - all rights reserved  
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG  
Flachsmarktstr. 8  
32825 Blomberg  
Germany  
Tel. +49 5235 300  
Fax +49 5235 3 41200  
<http://www.phoenixcontact.com>

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1705196](#)