

PCB terminal block - SPT 16/ 1-V-10,0 WH - 1708575

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




PCB terminal block, nom. voltage: 1000 V, pitch: 10 mm, number of positions: 1, connection method: Push-in spring connection, mounting: Wave soldering, color: white


The figure shows the standard item

Your advantages

- Time saving push-in connection, tools not required
- Defined contact force ensures that contact remains stable over the long term
- Clamping space opened by means of fixed screwdriver enables convenient conductor connection
- Vertical connection enables multi-row arrangement on the PCB



Key Commercial Data

Packing unit	50 pc
GTIN	 4 055626 014074
GTIN	4055626014074

Technical data

Dimensions

Length [l]	29 mm
Pitch	10 mm
Width [w]	11.8 mm
Height	31.3 mm
Height [h]	35.4 mm
Solder pin [P]	4.1 mm
Pin spacing	15 mm
Hole diameter	1.7 mm

General

Range of articles	SPT 16/..-V
Nominal cross section	16 mm²

PCB terminal block - SPT 16/ 1-V-10,0 WH - 1708575

Technical data

General


Number of positions	1
---------------------	---

Environmental Product Compliance


China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Drawings

Drilling diagram



Dimensional drawing



Approvals

Approvals

Approvals

IECEE CB Scheme / SEV / EAC / cULus Recognized

Ex Approvals

Approval details


IECEE CB Scheme		http://www.iecee.org/	CH-8077
Nominal voltage UN	1000 V		
Nominal current IN	76 A		


SEV		https://www.electrosuisse.ch/de/meta/shop/produktezertifikate.html	IK-3431
Nominal voltage UN	1000 V		

PCB terminal block - SPT 16/ 1-V-10,0 WH - 1708575

Approvals

Nominal current IN	76 A
mm ² /AWG/kcmil	16

EAC		B.01742
-----	---	---------

cULus Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	E60425-20061129
	D	B	C
Nominal voltage UN	300 V	300 V	150 V
Nominal current IN	10 A	66 A	66 A
mm ² /AWG/kcmil	20-4	20-4	20-4

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1708575](#)