


PCB terminal block - SPT 5/ 6-H-7,5-ZB MIX GY/BU - 1711041

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




PCB terminal block, nominal current: 41 A, pitch: 7.5 mm, number of positions: 6, connection method: Push-in spring connection, mounting: Wave soldering, color: multi-color

The figure shows a 5-pos. version of the product



Key Commercial Data

Packing unit	50 pc
GTIN	 4 055626 202099
GTIN	4055626202099

Technical data

Item properties

Number of positions	6
Pin layout	Zigzag pinning W

Dimensions for the product

Width [w]	46.8 mm
Height [h]	19 mm
Pitch	7.5 mm
Height (without solder pin)	14.4 mm
Solder pin [P]	4.6 mm
Pin spacing	13.2 mm
Dimension a	37.5 mm

Dimensions for PCB design

Hole diameter	2.1 mm
Pin spacing	13.2 mm

Packaging information

Type of packaging	packed in cardboard
-------------------	---------------------

PCB terminal block - SPT 5/ 6-H-7,5-ZB MIX GY/BU - 1711041

Technical data

Packaging information

Pieces per package	50
Denomination packing units	Pcs.

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Approvals

Approvals


Approvals


CCA / IECCEB Scheme / SEV / EAC / cULus Recognized

Ex Approvals

Approval details

CCA	IK-2956
Nominal voltage UN	1000 V
Nominal current IN	41 A
mm ² /AWG/kcmil	6

IECEE CB Scheme		http://www.iecee.org/	CH-7429
Nominal voltage UN	1000 V		
Nominal current IN	41 A		
mm ² /AWG/kcmil	6		


SEV		https://www.electrosuisse.ch/de/meta/shop/produktezertifikate.html	IK-3150
Nominal voltage UN	1000 V		
Nominal current IN	41 A		

PCB terminal block - SPT 5/ 6-H-7,5-ZB MIX GY/BU - 1711041

Approvals

mm ² /AWG/kcmil	6
----------------------------	---

EAC		B.01742
-----	---	---------

cULus Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	E60425-20061129
	B	C	
Nominal voltage UN	600 V	600 V	
Nominal current IN	36 A	36 A	
mm ² /AWG/kcmil	24-8	24-8	

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1711041](#)