

PCB terminal block - SPT 5/ 1-V-7,5 GTBU - 1708474

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




PCB terminal block, nom. voltage: 1000 V, pitch: 7.5 mm, number of positions: 1, connection method: Push-in spring connection, mounting: Wave soldering, color: gentian blue


The figure shows a 1-pos. version of the product

Your advantages

- Time saving push-in connection, tools not required
- Defined contact force ensures that contact remains stable over the long term
- Clamping space opened by means of fixed screwdriver enables convenient conductor connection
- Vertical connection enables multi-row arrangement on the PCB



Key Commercial Data

Packing unit	50 pc
GTIN	 4 055626 022390
GTIN	4055626022390

Technical data

Dimensions

Length [l]	18.5 mm
Pitch	7.5 mm
Width [w]	9.3 mm
Height	24.15 mm
Height [h]	28.75 mm
Solder pin [P]	4.6 mm
Pin spacing	14 mm
Hole diameter	2.1 mm

General

Range of articles	SPT 5/..-V
Nominal cross section	6 mm ²

PCB terminal block - SPT 5/ 1-V-7,5 GTBU - 1708474

Technical data

General

Number of positions	1
---------------------	---

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Approvals


Approvals


Approvals

IECEE CB Scheme / SEV / EAC / cULus Recognized

Ex Approvals

Approval details


IECEE CB Scheme		http://www.iecee.org/	CH-7429
Nominal voltage UN	450 V		
Nominal current IN	41 A		
mm ² /AWG/kcmil	6		

SEV		https://www.electrosuisse.ch/de/meta/shop/produktezertifikate.html	IK-3150
Nominal voltage UN	450 V		
Nominal current IN	41 A		
mm ² /AWG/kcmil	6		

EAC		B.01742
-----	---	---------

PCB terminal block - SPT 5/ 1-V-7,5 GTBU - 1708474

Approvals

cULus Recognized		http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm	E60425-20061129
	D	B	C
Nominal voltage UN	600 V	300 V	150 V
Nominal current IN	5 A	36 A	36 A
mm ² /AWG/kcmil	24-8	24-8	24-8

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1708474](#)