

Electronic housing - ME 22,5 UT/FE BUS/10 GNTQ - 2709901

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Component housing, length: 99 mm, Lower part, color: green/turquoise, width: 22.5 mm, height: 114.5 mm

Your advantages

- Item is from the ME product range
- Tool-free mounting
- Available in overall widths from 12.5 mm to 90 mm, modular extension is possible
- Inflammability class V0 according to UL 94
- Variety of connection technologies
- Can be mounted on the DIN rail
- Optional bus connector that is either integrated or mounted on the DIN rail



Key Commercial Data

Packing unit	50 pc
GTIN	
GTIN	4017918884062

Technical data

General

Housing type	Component housing
Housing material	Polyamide
Color (RAL)	green/turquoise (5018)

Ambient conditions

Ambient temperature (storage/transport)	-40 °C ... 70 °C
Ambient temperature (assembly)	-5 °C ... 100 °C
Ambient temperature (operation)	-40 °C (depending on power dissipation)

Dimensions

Length	99 mm
--------	-------

Electronic housing - ME 22,5 UT/FE BUS/10 GNTQ - 2709901

Technical data

Dimensions

Height	114.5 mm
Width	22.5 mm
Depth	99 mm
	102 mm

Technical data

Connection in acc. with standard	CUL
Nominal voltage U_N	300 V
Nominal current I_N	8 A
Indicator1	CUL1
Power dissipation without gap	6.1 W
Power dissipation with 20 mm gap	12.1 W
Number of positions	16
	4
	24

Standards and Regulations

Connection in acc. with standard	CUL
Flammability rating according to UL 94	V0

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Approvals


Approvals

Approvals

cUL Recognized / null / null / null / null / null / null / null / null / cULus Recognized


Ex Approvals

Approval details

cUL Recognized		http://database.ul.com/cgi-bin/XYVV/template/LISEXT/1FRAME/index.htm	FILE E 60425
	D	B	
Nominal voltage U_N	300 V	300 V	
Nominal current I_N	8 A	8 A	

Electronic housing - ME 22,5 UT/FE BUS/10 GNTQ - 2709901

Approvals

<p>cULus Recognized</p> 

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>
 PHOENIX CONTACT GmbH & Co. KG
 Flachsmarktstr. 8
 32825 Blomberg
 Germany
 Tel. +49 5235 300
 Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[2709901](#)