


PCB terminal block - ZFKDSA 2,5-5,08-15 - 1710484

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)


PCB terminal block, nominal current: 24 A, nom. voltage: 400 V, pitch: 5.08 mm, number of positions: 15, connection method: Spring-cage connection, mounting: Wave soldering, color: green. The article can be aligned to create different nos. of positions!



The figure shows the 10-pos. standard item

Your advantages

- Defined contact force ensures that contact remains stable over the long term
- Clamping space opened by means of fixed screwdriver enables convenient conductor connection
- Angled connection enables multi-row arrangement on the PCB
- The latching on the side enables various numbers of positions to be combined
- Two solder pins reduce the mechanical strain on the soldering spots



Key Commercial Data

| | |
|--------------|---------------|
| Packing unit | 50 pc |
| GTIN | |
| GTIN | 4055626156378 |

Technical data

Dimensions

| | |
|----------------|---------|
| Pitch | 5.08 mm |
| Solder pin [P] | 3.5 mm |
| Hole diameter | 1.3 mm |

General

| | |
|--|---------------------|
| Range of articles | ZFKDS(A) 2,5 |
| Insulating material group | I |
| Rated voltage (III/2) | 400 V |
| Nominal current I _N | 24 A |
| Nominal cross section | 2.5 mm ² |
| Flammability rating according to UL 94 | V0 |

PCB terminal block - ZFKDSA 2,5-5,08-15 - 1710484

Technical data

General

| | |
|---------------------|----|
| Number of positions | 15 |
|---------------------|----|

Standards and Regulations

| | |
|--|----|
| Flammability rating according to UL 94 | V0 |
|--|----|

Environmental Product Compliance

| | |
|------------|---|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
| | No hazardous substances above threshold values |

Approvals


Approvals

Approvals

EAC

Ex Approvals

Approval details

| | | |
|-----|---|---------|
| EAC |  | B.01742 |
|-----|---|---------|

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1710484](#)