


Printed-circuit board connector - TVFKC 1,5/ 3-ST CP1,3 BD:-24SO - 1711672

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

PCB connector, nominal current: 10 A, rated voltage (III/2): 320 V, number of positions: 3, pitch: 5 mm, connection method: Push-in spring connection, color: green, contact surface: Tin




The figure shows a 10-position version of the product

Your advantages

- ✓ Time saving push-in connection, tools not required
- ✓ Potentials can be easily looped through – ideal for BUS applications
- ✓ Intuitive use through colour coded actuation lever
- ✓ Can be combined with the MSTB 2,5 range
- ✓ Quick and convenient testing using integrated test option



Key Commercial Data

| | |
|--------------|---|
| Packing unit | 50 pc |
| GTIN |  4 055626 251264 |
| GTIN | 4055626251264 |

Technical data

Dimensions

| | |
|-------------|-------|
| Width [w] | 10 mm |
| Pitch | 5 mm |
| Dimension a | 5 mm |

General

| | |
|---------------------------|---------------------------|
| Range of articles | TVFKC 1,5/..-ST |
| Number of positions | 3 |
| Connection method | Push-in spring connection |
| Insulating material group | I |

Printed-circuit board connector - TVFKC 1,5/ 3-ST CP1,3 BD:-24SO - 1711672

Technical data

General

| | |
|--|---------------------|
| Rated voltage (III/2) | 320 V |
| Nominal current I _N | 10 A |
| Nominal cross section | 1.5 mm ² |
| Flammability rating according to UL 94 | V0 |

Standards and Regulations

| | |
|--|----|
| Flammability rating according to UL 94 | V0 |
|--|----|

Environmental Product Compliance

| | |
|------------|---|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
| | No hazardous substances above threshold values |

Approvals

Approvals

Approvals

cULus Recognized

Ex Approvals

Approval details

| | | | |
|----------------------------|-------|---|-----------------|
| cULus Recognized | | http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm | E60425-19931012 |
| | D | B | |
| Nominal voltage UN | 300 V | 300 V | |
| Nominal current IN | 8 A | 8 A | |
| mm ² /AWG/kcmil | 24-16 | 24-16 | |

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
 Flachsmarktstr. 8
 32825 Blomberg
 Germany
 Tel. +49 5235 300
 Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1711672](#)