

PCB terminal block - PTS 1,5/16-5,0-H - 1712658

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)


PCB terminal block, nominal current: 16 A, nom. voltage: 400 V, pitch: 5 mm, number of positions: 16, connection method: Push-in spring connection, mounting: Wave soldering, color: green




The figure shows the 10-position version

Your advantages

- ✓ Time saving push-in connection, tools not required
- ✓ Defined contact force ensures that contact remains stable over the long term
- ✓ Finger-operated release button for very convenient operation
- ✓ Quick and convenient testing using integrated test option
- ✓ Largest possible clamping space in a small component size



Key Commercial Data

Packing unit	50 pc
GTIN	 4 055626 291048
GTIN	4055626291048

Technical data

Dimensions

Length [l]	10.5 mm
Pitch	5 mm
Dimension a	75 mm
Width [w]	10 mm
Height	13.6 mm
Height [h]	16.1 mm
Solder pin [P]	2.5 mm
Hole diameter	1.2 mm

General

Range of articles	PTS 1,5/..-H
-------------------	--------------

PCB terminal block - PTS 1,5/16-5,0-H - 1712658

Technical data

General

Insulating material group	I
Rated voltage (III/2)	400 V
Nominal current I _N	16 A
Nominal cross section	1.5 mm ²
Flammability rating according to UL 94	V0
Number of positions	16

Standards and Regulations

Flammability rating according to UL 94	V0
--	----

Environmental Product Compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

Approvals


Approvals

Approvals

cULus Recognized

Ex Approvals

Approval details

cULus Recognized  http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm E60425-20030527		
	D	B
Nominal voltage UN	300 V	300 V
Nominal current IN	15 A	15 A
mm ² /AWG/kcmil	26-14	26-14

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1712658](#)