

Feed-through header - MCV 1,5/10-G-3,5 YE - 1713148

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)


PCB headers, nominal current: 8 A, rated voltage (III/2): 160 V, number of positions: 10, pitch: 3.5 mm, color: yellow, contact surface: Tin




The figure shows a 10-position version of the product

Your advantages

- ✓ Well-known mounting principle allows worldwide use
- ✓ Vertical connection enables multi-row arrangement on the PCB
- ✓ Maximum flexibility when it comes to device design – one header for connectors with different connection technologies



Key Commercial Data

| | |
|--------------|---|
| Packing unit | 100 pc |
| GTIN |  4 055626 305875 |
| GTIN | 4055626305875 |

Technical data

Dimensions

| | |
|--------------------------|--------------|
| Length [l] | 7.25 mm |
| Width | 36.4 mm |
| Pitch | 3.5 mm |
| Dimension a | 31.5 mm |
| Width [w] | 36.4 mm |
| Height [h] | 12.6 mm |
| Height | 9.2 mm |
| Length of the solder pin | 3.4 mm |
| Pin dimensions | 0.8 x 0.8 mm |
| Length | 7.25 mm |

General

Feed-through header - MCV 1,5/10-G-3,5 YE - 1713148

Technical data

General

| | |
|--------------------------------|---------------|
| Range of articles | MCV 1,5/...-G |
| Rated voltage (III/2) | 160 V |
| Nominal current I _N | 8 A |
| Color | yellow |
| Number of positions | 10 |

Environmental Product Compliance

| | |
|------------|---|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
| | No hazardous substances above threshold values |

Approvals


Approvals


Approvals


IECEE CB Scheme / VDE Gutachten mit Fertigungsüberwachung / EAC / cULus Recognized

Ex Approvals

Approval details


| | | | |
|--------------------------------|---|---|----------------|
| IECEE CB Scheme |  | http://www.iecee.org/ | DE1-60987-B1B2 |
| Nominal voltage U _N | 160 V | | |
| Nominal current I _N | 8 A | | |

| | | | |
|---|---|---|----------|
| VDE Gutachten mit Fertigungsüberwachung |  | http://www2.vde.com/de/Institut/Online-Service/VDE-gepruefteProdukte/Seiten/Online-Suche.aspx | 40011723 |
| Nominal voltage U _N | 160 V | | |
| Nominal current I _N | 8 A | | |

| | | |
|-----|---|---------|
| EAC |  | B.01742 |
|-----|---|---------|

Feed-through header - MCV 1,5/10-G-3,5 YE - 1713148

Approvals

| | | | |
|--------------------|---|---|-----------------|
| cULus Recognized |  | http://database.ul.com/cgi-bin/XYV/template/LISEXT/1FRAME/index.htm | E60425-20110128 |
| | D | B | |
| Nominal voltage UN | 300 V | 300 V | |
| Nominal current IN | 8 A | 8 A | |

Phoenix Contact 2018 © - all rights reserved
<http://www.phoenixcontact.com>

PHOENIX CONTACT GmbH & Co. KG
Flachsmarktstr. 8
32825 Blomberg
Germany
Tel. +49 5235 300
Fax +49 5235 3 41200
<http://www.phoenixcontact.com>

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Phoenix Contact:](#)

[1713148](#)